



# S8440

F32/25WT8 /841 /ES /ENV  
25 watt; T8; Fluorescent; 4100K Cool White; 85 CRI; Medium Bi  
Pin base

### Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8440

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8440	045923084409	25	T8	Medium Bi Pin	G13	F32/25WT8 /841 /ES /ENV	1.00"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	IS Rated Hours	RS/PRS Rated Hours	Kelvin Temp
47.78"	48"	2400	2280	30000	24000	30000	4100
Color	Pack	CRI	RoHS Compliant		CEE Qualified		
Cool White	30	85	Yes		Yes		



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S8440

F32/25WT8 /841 /ES /ENV  
25 watt; T8; Fluorescent; 4100K Cool White; 85 CRI; Medium Bi  
Pin base

### Features

- High Performance and Efficiency
- TCLP compliant
- Meets RoHS standards



S8440

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	MOD In Inches
S8440	045923084409	25	T8	Medium Bi Pin	G13	F32/25WT8 /841 /ES /ENV	1.00"
MOL In Inches	Nominal Length	Initial Lumens	Mean Lumens	Average Rated Hours	IS Rated Hours	RS/PRS Rated Hours	Kelvin Temp
47.78"	48"	2400	2280	30000	24000	30000	4100
Color	Pack	CRI	RoHS Compliant		CEE Qualified		
Cool White	30	85	Yes		Yes		



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

