



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S8738 \*Delisted\* 20W Led A21 50K E26 120-277V 2910LM

Satco

Catalog Number	S8738
Manufacturer	Satco
Description	20 Watt Led A21 Hi-Pro High Lumen Output Lamp - 5000K - Medium Base - 120-277 Volts
Weight per unit	0.6500 (lbs/each)
Product Category	Led A-Line A Shape Lamps

### Features

average life	25000
connection	Medium
Fixture Type	Type A
lumens	2910
Warranty	5 Year Limited - Hi-Pro
Wattage	20

### Material, Color, and Finish

Color	White
-------	-------

### Dimensions and Weight

Size	MOL: 5, MOD: 2.63
------	-------------------

### Descriptions

Description	*DELISTED* 20W LED A21 50K E26 120-277V 2910LM
extra long description	SATCO S8738 20WA21/LED/HID/5000K/12
Long Description	20 Watt LED A21 Hi-Pro High Lumen Output Lamp - 5000K - Medium Base - 120-277 Volts
Product Type	20WA21/Led/5000K/120-277V/E26
Special Features	Burning Position: Universal;Common Purpose: Bollard and Post Top Lighting;Dimmable: Yes Dimmable - 120V only;Minimum Compartment Size: Width 6 in. Length 6 in. Depth 8.50 in.;Operating Temp: -20C (-4F) to a maximum of +45C (+113F);SDS Class: LED_Lamp

### Manufacturer Information

Brand	Satco
GTIN	00045923087387
Manufacturers Part Number	S8738
UPC	045923087387

### Taxonomies, Classifications, and Categories

Category Description	LED A-LINE SHAPE LAMPS
Type	Lamps



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	12
Weight Per each	0.65

## Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
standard	cULus- Dry