



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S8849 4.5G25/CL/Led/E26/40K/120V

Satco

Catalog Number	S8849
Manufacturer	Satco
Description	Satco S8849 4.5G25/CL/Led/E26/40K/1
Weight per unit	0.2600 (lbs/each)
Product Category	Led Decorative C, Ca, F, G Sha

Features

average life	15000
Base	Medium
beam angle	360
dimmable	Yes
lumens	450
Shape	G25
Voltage Rating	120
Warranty	3 Year Limited
Wattage	5

Material, Color, and Finish

color temperature	4000
-------------------	------

Dimensions and Weight

Diameter	3.13
Length	4.38

Descriptions

Description	4.5G25/CL/LED/E26/40K/120V
Long Description	SATCO S8849 4.5G25/CL/LED/E26/40K/1
Product Type	4.5G25/CL/Led/E26/40K/120V
Special Features	Operating Temp: -20C (-4F) to a maximum of +45C (+113F) ; Safety Listing: cULus - Damp ; SDS Class: LED_Lamp ; 3 Year Limited Warranty ; Enclosed fixture rated: Yes ; Cool white color temperature ; Incandescent equivalent: 40 Watts

Manufacturer Information

Brand	Satco
GTIN	00045923088490
Manufacturers Part Number	S8849
sub brand	Satco
UPC	045923088490

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	LED Filament



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Manufacturer Status Inactive

Packaging

Carton 1

Weight Per each 0.26

Uses, Certifications, and Standards

Operating Temperature -20C (-4F) to a maximum of +45C (+113F)