



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S9002 8W Led R20 Med Base 3000K

Satco

Catalog Number	S9002
Manufacturer	Satco
Description	BR Led Lamp, Designation: 8R20/Led/3000K/520L/120V/D, 120 V, 8 WTT, R20 Shape, E26 Medium Base, Frosted, 25000 HR, Lumens: 520 LM Initial, 3000 Deg K Color Temperature, Warm White 80 Cri, 106 Deg Beam Angle, 3-15/16 In Length, 2-15/32 In Diameter
Weight per unit	0.2400 (lbs/each)
Product Category	Lighting

Features

average life	25000 HR
Base	Medium
beam angle	106 V
lumens	ALUMINUM ALLOY
Shape	R20
Voltage Rating	ELBOW FITTING, 316 STAINLESS STEEL MATERIAL; 1/2 INCH SIZE A; 1/2 INCH SIZE B; .5 SIZE A - DECIMAL; .5 SIZE B - DECIMAL; 1/2 SIZE A - FRACTIONAL; 1/2 SIZE B - FRACTIONAL; NUCLEAR, PHARMACEUTICAL INDUSTRY CHEMICAL, PETROCHEMICAL APPLICATION; CAST PROCESS
Wattage	8 Each

Material, Color, and Finish

Color	FROST
color rendering index (cri)	80 A
color temperature	3000 k

Dimensions and Weight

Diameter	2.47 in
Length	3.94 in



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	8W LED R20 MED BASE 3000K
Long Description	BR LED Lamp, Designation: 8R20/LED/3000K/520L/120V/D, 120 V, 8 WTT, R20 Shape, E26 Medium Base, Frosted, 25000 HR, Lumens: 520 LM Initial, 3000 DEG K Color Temperature, Warm White 80 CRI, 106 DEG Beam Angle, 3-15/16 IN Length, 2-15/32 IN Diameter
Product Type	8R20/Led/3000K/520L/120V/D
Special Features	ENERGY STAR; Dimmable

Manufacturer Information

Brand	Satco
GTIN	00045923090028
Manufacturers Part Number	S9002
sub brand	DITTO
UPC	045923090028

Taxonomies, Classifications, and Categories

Category Description	DECORATIVE RESIDENTIAL
Type	BR LED

Packaging

Carton	6
Package	24
Weight Per each	0.24

Uses, Certifications, and Standards

standard	UL or ETL Listed; RoHS Compliant
----------	----------------------------------