



S9014

7PAR20/LED /40' /3500K /WH /IP65
7 watt; PAR20 LED; 3500K; 40' beam spread; Medium base;
120 volts

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable
- IP65 - Indoor / Outdoor Use

Top 3 Recommended Dimmers

- Lutron® CL Family (96-101)
- Legrand® ADTP703TU (TRU Universal)
- Cooper® TAL06P-C1



S9014

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S9014	045923090141	7	PAR20	Medium	E26	7PAR20/LED /40' /3500K /WH /IP65	120
Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI
White	3.43"	2.50"	400	25000	3500	Neutral White	83
Pack	Package Type	Beam Spread	ENERGY STAR	RoHS Compliant	UL or ETL Listed		
24/6	Box	40	ENERGY STAR	Yes	Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9014

7PAR20/LED /40' /3500K /WH /IP65
7 watt; PAR20 LED; 3500K; 40' beam spread; Medium base;
120 volts

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable
- IP65 - Indoor / Outdoor Use

Top 3 Recommended Dimmers

- Lutron® CL Family (96-101)
- Legrand® ADTP703TU (TRU Universal)
- Cooper® TAL06P-C1



S9014

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S9014	045923090141	7	PAR20	Medium	E26	7PAR20/LED /40' /3500K /WH /IP65	120
Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI
White	3.43"	2.50"	400	25000	3500	Neutral White	83
Pack	Package Type	Beam Spread	ENERGY STAR	RoHS Compliant	UL or ETL Listed		
24/6	Box	40	ENERGY STAR	Yes	Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

