



S9037

10.5A19/OMNI/LED/2700K
10.5 watt; A19 LED; 2700K; Medium base; 360° beam spread;
120 volts

Features

- Solid State LED lighting
- A shaped replacement lamp
- Long life
- Dimmable

Top 3 Recommended Dimmers

- Lutron® CL Family (96-101)
- Lutron® CT-603PGH Incandescent
- Cooper® TAL06P-C1



S9037

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S9037	045923090370	10.5	A19	Medium	E26	10.5A19/OMNI/LED/2700K	120
MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Incandescent Equivalent
4.5"	2.38"	810	25000	2700	Warm White	80	60W
Pack	Package Type	Beam Spread	ENERGY STAR	RoHS Compliant	UL or ETL Listed		
24/6	Box	360	ENERGY STAR	Yes	Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

