



# S9094

17PAR38/LED/40'/3000K/120V  
17 watt; LED PAR38 LED; 3000K; 40' beam spread; Medium base; 120 volts

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Energy Saver
- Dimmable

### Top 3 Recommended Dimmers

- Lutron® CL Family (96-101)
- Leviton® 6674 Universal
- Lutron® MACL-153 Maestro®



S9094

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S9094	045923090943	17	PAR38	Medium	E26	17PAR38/LED/40'/3000K/120V	120
MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Pack
5.16"	4.75"	1200	25000	3000	Warm White	80	12/6
Package Type	Beam Spread	ENERGY STAR	RoHS Compliant	UL or ETL Listed			
Box	40	ENERGY STAR	Yes	Yes			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9094

17PAR38/LED/40'/3000K/120V  
17 watt; LED PAR38 LED; 3000K; 40' beam spread; Medium base; 120 volts

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Energy Saver
- Dimmable

### Top 3 Recommended Dimmers

- Lutron® CL Family (96-101)
- Leviton® 6674 Universal
- Lutron® MACL-153 Maestro®



S9094

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S9094	045923090943	17	PAR38	Medium	E26	17PAR38/LED/40'/3000K/120V	120

MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Pack
5.16"	4.75"	1200	25000	3000	Warm White	80	12/6

Package Type	Beam Spread	ENERGY STAR	RoHS Compliant	UL or ETL Listed
Box	40	ENERGY STAR	Yes	Yes



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

