



# S9096

7MR16/LED/40°/3K/120V/GU10  
7 watt; LED MR16 LED; 3000K; 40° beam spread; GU10 base;  
120 volts

### Features

- Solid State LED lighting
- High Efficacy
- Long life
- Dimmable

### Top 3 Recommended Dimmers

- Lutron® CL Family (96-101)
- Leviton® 6674 Universal
- Leviton® IPLO6 Universal



S9096

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S9096	045923090967	7	MR16	GU10	GU10	7MR16/LED/40°/3K/120V/GU10	120
MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Pack
2.165"	2.00"	520	25000	3000	Warm White	80	48/12
Package Type	Beam Spread	ENERGY STAR	RoHS Compliant	UL or ETL Listed			
Box	40	ENERGY STAR	Yes	Yes			



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

