



# S9106

7MR16/LED/40°/5K/12V/DIM  
7 watts; MR16 LED; GU5.3 base; 40° beam spread; 5000K; 12 volts; Dimmable

### Features

- Solid State LED lighting
- High Efficacy
- Long life
- UL approved for totally enclosed fixtures
- Dimmable

### Compatible Dimmers

- Lutron® SELV300 ELV - Use with electronic low-voltage transformer
- Lutron® SLV600P (MLV) - Use with magnetic low-voltage transformer



S9106

| Item Number | UPC           | Watts          | Lamp Shape       | Base                | ANSI Base   | Lamp Code                | Voltage |
|-------------|---------------|----------------|------------------|---------------------|-------------|--------------------------|---------|
| S9106       | 045923091063  | 7              | MR16             | GU5.3               | GU5.3       | 7MR16/LED/40°/5K/12V/DIM | 12      |
| Finish      | MOL In Inches | MOD In Inches  | Initial Lumens   | Average Rated Hours | Kelvin Temp | Color                    | CRI     |
| White       | 1 7/8"        | 2              | 560              | 25000               | 5000        | Natural Light            | 80      |
| Pack        | Beam Spread   | RoHS Compliant | UL or ETL Listed |                     |             |                          |         |
| 12/48       | 40            | Yes            | Yes              |                     |             |                          |         |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9106

7MR16/LED/40°/5K/12V/DIM  
7 watts; MR16 LED; GU5.3 base; 40° beam spread; 5000K; 12 volts; Dimmable

### Features

- Solid State LED lighting
- High Efficacy
- Long life
- UL approved for totally enclosed fixtures
- Dimmable

### Compatible Dimmers

- Lutron® SELV300 ELV - Use with electronic low-voltage transformer
- Lutron® SLV600P (MLV) - Use with magnetic low-voltage transformer



S9106

| Item Number | UPC           | Watts          | Lamp Shape       | Base                | ANSI Base   | Lamp Code                | Voltage |
|-------------|---------------|----------------|------------------|---------------------|-------------|--------------------------|---------|
| S9106       | 045923091063  | 7              | MR16             | GU5.3               | GU5.3       | 7MR16/LED/40°/5K/12V/DIM | 12      |
| Finish      | MOL In Inches | MOD In Inches  | Initial Lumens   | Average Rated Hours | Kelvin Temp | Color                    | CRI     |
| White       | 1 7/8"        | 2              | 560              | 25000               | 5000        | Natural Light            | 80      |
| Pack        | Beam Spread   | RoHS Compliant | UL or ETL Listed |                     |             |                          |         |
| 12/48       | 40            | Yes            | Yes              |                     |             |                          |         |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

