



S9134

10BR30/LED/3000K/800L/120V/D
10 watt; BR30 LED; 108' beam spread; 3000K; Medium base;
120 volts; Dimmable

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable

Top 3 Recommended Dimmers

- Lutron® CT-600P
- Leviton® 6674 Universal
- Leviton® IPLO6 Universal



S9134

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S9134	045923091346	10	BR30	Medium	E26	10BR30/LED/3000K/800L/120V/D	120
Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI
Frosted	5 3/16"	3.75"	800	25000	3000	Warm White	80
Incandescent Equivalent	Pack	Package Type	Beam Spread	ENERGY STAR	RoHS Compliant	UL or ETL Listed	
65W	12/6	Box	108	ENERGY STAR	Yes	Yes	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

