



S9383

6.5MR16/LED/40°/30K/120V/GU10
6.5 watt; LED MR16 LED; 3000K; 40° beam spread; GU10 base; 120 volts

Features

- Solid State LED lighting
- High Efficacy
- Long life
- Dimmable
- UL approved for totally enclosed fixtures



S9383

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	Lamp Code		
S9383	045923093838	120	6.5	50W	MR16	GU10	6.5MR16/LED/40°/30K/120V/GU10		
Dimmable/Non-Dimmable		MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	
Dimmable		2 3/16"	2.00"	520	25000	3000	Warm White	80	
Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant	UL or ETL Listed	Warranty			
40	48/12	Box	ENERGY STAR	Yes	Yes	3 Year Limited			



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

