



S9391

22W/LED/HID/5000K/100-277V
 22 watt - HID Replacement; 5000K; Medium base; 100-277 volts

Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP65 rated
- Base up, base down or horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- cULus listed

Additional Technical Specifications

- Power Factor >0.9
- Min Starting Temp -20°C
- Max Starting Temp 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Optional accessory: In-line surge protector [80-929](#)



S9391

Item Number	Product Line	UPC	Input Voltage	Watts	Incandescent Equivalent	Fluorescent Equivalent	HID Equivalent
S9391	Hi-Pro	045923093913	100 - 277	22	150W	40W	100W
Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens
Medium	E26	22W/LED/HID/5000K/100-277V	Non-Dimmable	White	8 1/16"	2.75"	2640
Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant
50000	5000	Natural Light	80+	300	48	Box	Yes
UL or ETL Listed						Warranty	
Yes						5 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9391

22W/LED/HID/5000K/100-277V
 22 watt - HID Replacement; 5000K; Medium base; 100-277 volts

Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP65 rated
- Base up, base down or horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- cULus listed

Additional Technical Specifications

- Power Factor >0.9
- Min Starting Temp -20°C
- Max Starting Temp 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Optional accessory: In-line surge protector [80-929](#)



S9391

Item Number	Product Line	UPC	Input Voltage	Watts	Incandescent Equivalent	Fluorescent Equivalent	HID Equivalent
S9391	Hi-Pro	045923093913	100 - 277	22	150W	40W	100W
Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens
Medium	E26	22W/LED/HID/5000K/100-277V	Non-Dimmable	White	8 1/16"	2.75"	2640
Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant
50000	5000	Natural Light	80+	300	48	Box	Yes
UL or ETL Listed						Warranty	
Yes						5 Year Limited	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

