



S9452

15PAR38/LED/60°/3500K/120V/D
 15 watt PAR38 LED; 3500K; 60° beam spread; Medium base;
 120 volts

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable

Compatible Dimmers

- Lutron® C.L Family of dimmers Gen 2.0-2.1-2.2
- Lutron® MAESTRO MACL-153
- Lutron® CASSETEA PPD-6WCL-WH



S9452

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base | ANSI Base |
|-------------|--------------|---------|-------|-------------------------|------------|--------|-----------|
| S9452 | 045923094521 | 120 | 15 | 90W | PAR38 | Medium | E26 |

| Lamp Code | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp |
|------------------------------|-----------------------|--------|---------------|---------------|----------------|---------------------|-------------|
| 15PAR38/LED/60°/3500K/120V/D | Dimmable | Silver | 5 3/16" | 4 3/4" | 1150 | 25000 | 3500 |

| Color | CRI | Beam Spread Deg | Pack | Package Type | ENERGY STAR | RoHS Compliant | UL or ETL Listed |
|---------------|-----|-----------------|------|--------------|-------------|----------------|------------------|
| Neutral White | 80 | 60 | 12/6 | Box | ENERGY STAR | Yes | Yes |

Warranty

[3 Year Limited](#)



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9452

15PAR38/LED/60°/3500K/120V/D
 15 watt PAR38 LED; 3500K; 60° beam spread; Medium base;
 120 volts

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable

Compatible Dimmers

- Lutron® C.L Family of dimmers Gen 2.0-2.1-2.2
- Lutron® MAESTRO MACL-153
- Lutron® CASSETA PPD-6WCL-WH



S9452

| Item Number | UPC | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base | ANSI Base |
|-------------|--------------|---------|-------|-------------------------|------------|--------|-----------|
| S9452 | 045923094521 | 120 | 15 | 90W | PAR38 | Medium | E26 |

| Lamp Code | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp |
|------------------------------|-----------------------|--------|---------------|---------------|----------------|---------------------|-------------|
| 15PAR38/LED/60°/3500K/120V/D | Dimmable | Silver | 5 3/16" | 4 3/4" | 1150 | 25000 | 3500 |

| Color | CRI | Beam Spread Deg | Pack | Package Type | ENERGY STAR | RoHS Compliant | UL or ETL Listed |
|---------------|-----|-----------------|------|--------------|-------------|----------------|------------------|
| Neutral White | 80 | 60 | 12/6 | Box | ENERGY STAR | Yes | Yes |

Warranty

[3 Year Limited](#)



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

