



S9544

3JC/G6.35/LED/3000K/12V/D
3 watt; JC LED; 3000K; G6.35 base; 12 volts

Features

- Solid State LED lighting
- High Efficacy
- Long life
- Dimmable

Silicon LED Replacements for Halogen G6.35 lamps.



S9544

Item Number	UPC	Voltage	Watts	Base	Lamp Code	Dimmable/Non-Dimmable	Finish
S9544	045923095443	12	3	G6.35	3JC/G6.35/LED/3000K/12V/D	Dimmable	Clear
MOL In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack
1 5/8"	300	25000	3000	Warm White	80	360	200/20
Package Type	RoHS Compliant	UL or ETL Listed	UL Classification				
Box	Yes	Yes	cETLus - Damp Location Rated				



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9544

3JC/G6.35/LED/3000K/12V/D
3 watt; JC LED; 3000K; G6.35 base; 12 volts

Features

- Solid State LED lighting
- High Efficacy
- Long life
- Dimmable

Silicon LED Replacements for Halogen G6.35 lamps.



S9544

Item Number	UPC	Voltage	Watts	Base	Lamp Code	Dimmable/Non-Dimmable	Finish
S9544	045923095443	12	3	G6.35	3JC/G6.35/LED/3000K/12V/D	Dimmable	Clear
MOL In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack
1 5/8"	300	25000	3000	Warm White	80	360	200/20
Package Type	RoHS Compliant	UL or ETL Listed	UL Classification				
Box	Yes	Yes	cETLus - Damp Location Rated				



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

