



# S9581

6.5ST19/CL/LED/E26/27K/120V  
 6.5 watt ST19 LED; Clear; Medium base; 2700K; 810 lumens;  
 120 volts

## Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 60 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures

## Compatible Dimmers

- Leviton 6674 Universal†
- Cooper TAL06P-C1†
- Lutron Nova TCL

† When used with incandescent dimmers, derate the dimmer's maximum load by 75%. Consult your local electrical code to ensure compliance.



S9581

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9581	045923095818	120	6.5	60W	ST19	Medium	E26
Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
6.5ST19/CL/LED/E26/27K/120V	Dimmable	Clear	5 1/2"	2 3/8"	810	15000	2700
Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	RoHS Compliant	UL or ETL Listed
Warm White	80	360	-20°C (-4°F) to a maximum of +45°C (113°F)	24/6	Box	Yes	Yes
UL Classification						Warranty	
cULus - Damp Location Rated						3 Year Limited	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9581

6.5ST19/CL/LED/E26/27K/120V  
 6.5 watt ST19 LED; Clear; Medium base; 2700K; 810 lumens;  
 120 volts

## Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 60 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures

## Compatible Dimmers

- Leviton 6674 Universal†
- Cooper TAL06P-C1†
- Lutron Nova TCL

† When used with incandescent dimmers, derate the dimmer's maximum load by 75%. Consult your local electrical code to ensure compliance.



S9581

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9581	045923095818	120	6.5	60W	ST19	Medium	E26
Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
6.5ST19/CL/LED/E26/27K/120V	Dimmable	Clear	5 1/2"	2 3/8"	810	15000	2700
Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	RoHS Compliant	UL or ETL Listed
Warm White	80	360	-20°C (-4°F) to a maximum of +45°C (113°F)	24/6	Box	Yes	Yes
UL Classification						Warranty	
cULus - Damp Location Rated						3 Year Limited	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

