



S9621

9.5BR30/LED/3000K/800L/120V/D
9.5 watt; BR30 LED; 105° beam spread; 3000K; Medium base;
120 volts; Dimmable

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9621

| Item Number | Product Line | UPC | Voltage | Watts | Incandescent Equivalent | Power Factor | Lamp Shape |
|------------------|-----------------------------|--------------------------------|-----------------|---------------|-------------------------|----------------|---------------------|
| S9621 | DiTTO | 045923096211 | 120 | 9.5 | 65W | 0.91 | BR30 |
| Base | ANSI Base | Lamp Code | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours |
| Medium | E26 | 9.5BR30/LED/3000K/800L/120V/D | Frosted | 5 3/16" | 3.75" | 800 | 25000 |
| Kelvin Temp | Color | CRI | Beam Spread Deg | Pack | Package Type | ENERGY STAR | RoHS Compliant |
| 3000 | Warm White | 80 | 105 | 12/6 | Box | ENERGY STAR | Yes |
| UL or ETL Listed | UL Classification | Warranty | | | | | |
| Yes | cULus - Damp Location Rated | 3 Year Limited | | | | | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9621

9.5BR30/LED/3000K/800L/120V/D
9.5 watt; BR30 LED; 105° beam spread; 3000K; Medium base;
120 volts; Dimmable

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9621

| Item Number | Product Line | UPC | Voltage | Watts | Incandescent Equivalent | Power Factor | Lamp Shape |
|------------------|--------------|-------------------------------|-----------------|---------------|-------------------------|--------------------------------|---------------------|
| S9621 | DiTTO | 045923096211 | 120 | 9.5 | 65W | 0.91 | BR30 |
| Base | ANSI Base | Lamp Code | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours |
| Medium | E26 | 9.5BR30/LED/3000K/800L/120V/D | Frosted | 5 3/16" | 3.75" | 800 | 25000 |
| Kelvin Temp | Color | CRI | Beam Spread Deg | Pack | Package Type | ENERGY STAR | RoHS Compliant |
| 3000 | Warm White | 80 | 105 | 12/6 | Box | ENERGY STAR | Yes |
| UL or ETL Listed | | UL Classification | | | | Warranty | |
| Yes | | cULus - Damp Location Rated | | | | 3 Year Limited | |



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

