



# S9636

11.5BR40/LED/4000K/1000L/120V  
11.5 watt; LED BR40; 4000K; 103' beam spread; Medium base;  
120 volts; Dimmable

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9636

| Item Number | Product Line | UPC          | Voltage | Watts | Incandescent Equivalent | Power Factor | Lamp Shape |
|-------------|--------------|--------------|---------|-------|-------------------------|--------------|------------|
| S9636       | DiTTO        | 045923096365 | 120     | 11.5  | 75W                     | 0.90         | BR40       |

  

| Base   | ANSI Base | Lamp Code                     | Dimmable/Non-Dimmable | Finish  | MOL In Inches | MOD In Inches | Initial Lumens |
|--------|-----------|-------------------------------|-----------------------|---------|---------------|---------------|----------------|
| Medium | E26       | 11.5BR40/LED/4000K/1000L/120V | Dimmable              | Frosted | 6 7/16"       | 5.00"         | 1000           |

  

| Average Rated Hours | Kelvin Temp | Color      | CRI | Beam Spread Deg | Pack | Package Type | RoHS Compliant |
|---------------------|-------------|------------|-----|-----------------|------|--------------|----------------|
| 25000               | 4000        | Cool White | 80  | 103             | 12/6 | Box          | Yes            |

  

| UL or ETL Listed | UL Classification           | Warranty                       |
|------------------|-----------------------------|--------------------------------|
| Yes              | cULus - Damp Location Rated | <a href="#">3 Year Limited</a> |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9636

11.5BR40/LED/4000K/1000L/120V  
11.5 watt; LED BR40; 4000K; 103' beam spread; Medium base;  
120 volts; Dimmable

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9636

| Item Number         | Product Line                | UPC                           | Voltage                        | Watts           | Incandescent Equivalent | Power Factor  | Lamp Shape     |
|---------------------|-----------------------------|-------------------------------|--------------------------------|-----------------|-------------------------|---------------|----------------|
| S9636               | DiTTO                       | 045923096365                  | 120                            | 11.5            | 75W                     | 0.90          | BR40           |
| Base                | ANSI Base                   | Lamp Code                     | Dimmable/Non-Dimmable          | Finish          | MOL In Inches           | MOD In Inches | Initial Lumens |
| Medium              | E26                         | 11.5BR40/LED/4000K/1000L/120V | Dimmable                       | Frosted         | 6 7/16"                 | 5.00"         | 1000           |
| Average Rated Hours | Kelvin Temp                 | Color                         | CRI                            | Beam Spread Deg | Pack                    | Package Type  | RoHS Compliant |
| 25000               | 4000                        | Cool White                    | 80                             | 103             | 12/6                    | Box           | Yes            |
| UL or ETL Listed    | UL Classification           |                               | Warranty                       |                 |                         |               |                |
| Yes                 | cULus - Damp Location Rated |                               | <a href="#">3 Year Limited</a> |                 |                         |               |                |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

