



S9640

16.5BR40/LED/4000K/1280L/120V
16.5 watt; LED BR40; 3000K; 103' beam spread; Medium base;
120 volts; Dimmable

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9640

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape
S9640	DiTTO	045923096402	120	16.5	75W	0.92	BR40

Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens
Medium	E26	16.5BR40/LED/4000K/1280L/120V	Dimmable	Frosted	6 7/16"	5.00"	1280

Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant
25000	4000	Cool White	80	103	12/6	Box	Yes

UL or ETL Listed	UL Classification	Warranty
Yes	cULus - Damp Location Rated	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027





S9640

16.5BR40/LED/4000K/1280L/120V
16.5 watt; LED BR40; 3000K; 103' beam spread; Medium base;
120 volts; Dimmable

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9640

Item Number	Product Line	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape
S9640	DiTTO	045923096402	120	16.5	75W	0.92	BR40
Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens
Medium	E26	16.5BR40/LED/4000K/1280L/120V	Dimmable	Frosted	6 7/16"	5.00"	1280
Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant
25000	4000	Cool White	80	103	12/6	Box	Yes
UL or ETL Listed	UL Classification		Warranty				
Yes	cULus - Damp Location Rated		3 Year Limited				



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

