



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S9827 4.5W Led G25 27K Frosted 420LM

Satco

| | |
|------------------|--|
| Catalog Number | S9827 |
| Manufacturer | Satco |
| Description | 4.5 Watt G25 Led - Soft White Finish - Medium Base - 2700K - 420 Lumens - 120 Volt |
| Weight per unit | 0.2600 (lbs/each) |
| Product Category | Led Decorative C, Ca, F, G Sha |

Features

| | |
|--------------|----------------|
| average life | 15000 |
| Base | Medium |
| beam angle | 360 |
| lumens | 420L |
| Shape | G25 |
| Warranty | 3 Year Limited |

Material, Color, and Finish

| | |
|-------------------|------------|
| color temperature | 2700 |
| Finish | Soft White |

Dimensions and Weight

| | |
|------|------|
| Size | 4.38 |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | 4.5W LED G25 27K FROSTED 420LM |
| extra long description | SATCO S9827 4.5G25/SW/LED/E26/27K/1 |
| Long Description | 4.5 Watt G25 LED - Soft White finish - Medium Base - 2700K - 420 Lumens - 120 Volt |
| Product Type | 4.5G25/SW/Led/E26/27K/120V |
| Special Features | Warranty: 3 Year Limited ; RoHS Compliant: Yes ; Dimmable: Yes ; Energy Star: Yes ; Color Temperature: Warm White |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Satco |
| GTIN | 00045923098277 |
| Manufacturers Part Number | S9827 |
| UPC | 045923098277 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | DECORATIVE RESIDENTIAL |
| Type | LED |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 24 |
| Package | 6 |
| Weight | 0.09 |
| Weight Per each | 0.26 |

Uses, Certifications, and Standards

| | |
|-----------------------|---|
| Operating Temperature | -17C (+1.4F) to a maximum of +45C (+113F) |
| standard | cULus |