

S9876 A19 LED

6.5A19/CL/LED/E26/27K/ES/120V

Lamp Type	LED
Bulb Type	A19
Base Type	E26
Wattage	6.5
Color Temperature	2700
Color Rendering Index CRI	80
Warranty	3 Year Limited



Lighting Facts Per Bulb

Brightness	800 lumens
Estimated Energy Cost	\$0.72
per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use.	
Average Life	13.7 years
Based on 3 hrs/day	
Light Appearance	
Energy Used	6 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S9876	LED	*20045923098769	120	6.5	60	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	6.5A19/CL/LED/E26/27K/ES/120V	Yes	n/a	4 1/8	2 3/8	800	15000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
2700	Warm White	80	360	24	Box	n/a	Yes

S9876 A19 LED

6.5A19/CL/LED/E26/27K/ES/120V

Lamp Type	LED
Bulb Type	A19
Base Type	E26
Wattage	6.5
Color Temperature	2700
Color Rendering Index CRI	80
Warranty	3 Year Limited



Lighting Facts Per Bulb

Brightness	800 lumens
Estimated Energy Cost	\$0.72
per year, based on 3 hrs/day, 11c/kWh. Energy cost depends on utility rates and light use.	
Average Life	13.7 years
Based on 3 hrs/day	
Light Appearance	
Energy Used	6 watts

Product Specifications

Item Number	Technology	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base
S9876	LED	*20045923098769	120	6.5	60	A19	Medium
ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL in inches	MOD in inches	Initial Lumens	Average Rated Hours
E26	6.5A19/CL/LED/E26/27K/ES/120V	Yes	n/a	4 1/8	2 3/8	800	15000
Kelvin Temp	Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant
2700	Warm White	80	360	24	Box	n/a	Yes