



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S9963 5.5W 30K Led Flame Tip

Satco

Catalog Number	S9963
Manufacturer	Satco
Description	Led Lamp, 3000 K, 500 LM Brightness (Lumens), 5.5 W, 120 V, Clear, 15000 H Average Life, Candelabra Base, Dimmable, 1-3/8 In Diameter, 3-7/8 In Height, -4 °F Operating Temperature, +113 °F Operating Temperature, 60 W, 3 Yr Warranty, 0.03 LB
Weight per unit	0.1000 (lbs/each)
Product Category	Led Lamps & Modules

Features

connection	Candelabra
Fixture Type	Decorative
lumens	500
Shape	CA11

Material, Color, and Finish

Color	Colorless
-------	-----------

Dimensions and Weight

Size	MOL: 4.69, MOD: 1.38
------	----------------------

Descriptions

Description	5.5W 30K LED FLAME TIP
Special Features	Dimmable: Yes Dimmable ; Operating Temp: -20C (-4F) to a maximum of +45C (+113F) ; SDS Class: LED_Lamp ; 80 CRI ; 3000K color temperature

Manufacturer Information

GTIN	00045923099632
sub brand	Satco
UPC	045923099632

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Lamps

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight Per each	0.1

Uses, Certifications, and Standards

Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
-----------------------	---