

Eaton's Wiring Devices
AL series dimmers



One dimmer.
Many solutions.

Featuring the latest in dimming technology

Lighting control you can count on

EATON

Powering Business Worldwide



Right dimmer. Every time.

Eaton's AL series dimmers offer flexibility in design with the latest dimming technology

Flexibility & innovation

Eaton's Wiring Devices AL series dimmers offer a versatile option for any dimming application - fine tune the dimming performance to match your exact needs and change colors as needed to suit any décor.

Color flexibility

Color change kits come with three color faceplates, offering design flexibility within one product. Select models are available in 4 different color combination packs.



- Single pole or 3-way wiring in one unit
- Separate ON/OFF and DIM/BRIGHT controls allow easy return to favorite light levels
- Interchangeable faceplates available in 4 different color change kit options



LA	W	V
----	---	---

C2 Color Kit
(Light Almond, White, Ivory)

BK	W	V
----	---	---

C4 Color Kit
(Black, White, Ivory)

BK	W	GY
----	---	----

C5 Color Kit
(Black, White, Gray)

RB	W	SG
----	---	----

C6 Color Kit
(Oil Rubbed Bronze, White, Silver Granite)



Count on flexibility -
one dimmer handles common lighting loads.

Count on lower inventory cost -
includes an interchangeable color kit.

Count on saving time and money -
the right dimmer every time!






Lighting control you can count on

AL series dimmers provide rating flexibility

Enjoy flexibility and optimal dimming performance with a variety of light sources and functionality

Dimmer features	Smart AL dimmer (AAL06)	Decorator AL dimmer (DAL06P)	Slide AL dimmer (SAL06P3)	Universal Triac dimmer (SUT7)	Toggle AL dimmer (TAL06P2)
Rapid start feature	Selectable ON or OFF	Fully adjustable	Fixed ON	-	Fully adjustable
Adjustable high-end trim	✓	-	-	-	-
Adjustable low-end trim	✓	✓	✓	✓	✓
Wiring configurations	Single pole or multi-location	Single pole or 3-way	Single pole or 3-way	Single pole or 3-way	Single pole or 3-way
Color change kits	✓	✓	-	-	✓

Rated for common lighting loads

	Dimmable Light-Emitting Diodes (LED)
	Dimmable Compact Fluorescent (CFL)
	Electronic & Magnetic Low-Voltage (ELV & MLV)
	Incandescent/Halogen (INC/HAL)
	Fluorescent (FLR)



AL series dimmers



AAL06

Single pole and multi-location

- Green LEDs indicate light level and preset
- Separate DIM/BRIGHT bar can be used to adjust preset level when lights are ON or OFF
- Air gap switch allows for manual disconnect during lamp changes

Color change faceplate options



AAL06 (PJS26W wallplate sold separately)

Smart AL series dimmers

Features

- Electro-mechanical push pad for ON/OFF operation with separate DIM/BRIGHT bar
- 10-second delayed OFF feature
- Selectable Rapid Start feature to ensure lamp start-up at low preset light levels
- LED light level display for presetting illumination levels and master/accessory units for multi-location control
- Adjustable high-end and low-end trimming
- No de-rating required for CFL/LED in multi-gang installations
- Each color package includes 3 colors

Smart dimmers, wire leads




Rating W	Rating V/AC	Compatible lamp types	Description	Color suffix	Catalog no.
300	120	Dimmable LED/CFL	Smart dimmer master, AL series, single pole/multi-location with presets and LEDs. Neutral required.	C2, C4, C5	□ AAL06-___
600	120	INC, HAL, FLR, MLV, ELV			
—	120	—	Accessory dimmer, multi-location with presets and LEDs. Must be used with AAL06	B, BK, GY, LA, V, W, C2	□ ARD-___
—	—	—	Master dimmer color change faceplate	B, BK, GY, LA, V, W	□ AMC-___-BP
—	—	—	Accessory dimmer color change faceplate	B, BK, GY, LA, V, W	□ ARC-___-BP

See instruction sheet for de-rating information

Color ordering information

For ordering devices, include Cat. no. followed by the color code: B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White), C2 (Color Change Kit - Light Almond, White, Ivory), C4 (Color Change Kit - Black, White, Ivory), C5 (Color Change Kit - Black, White, Gray)



Compliances, specifications and availability are subject to change without notice.

AL series dimmers



DAL06P

Single pole and 3-way

- Separate DIM/BRIGHT bars allows lights to be returned to favorite settings
- Adjustable low-end trim setting improves lamp compatibility
- Fully adjustable Rapid Start ensures the right amount of power boost during start-up

Color change faceplate options



DAL06P
(PJS26W wallplate
sold separately)

Decorator AL series dimmers

Features

- Preset feature allows user to return to previous light level when turning lights ON
- Adjustable low-end dimming range
- Fully adjustable Rapid Start setting for optimal lamp start-up at low preset light levels
- No de-rating required in multi-gang installations
- Each color kit package includes 3 colors

Decorator dimmers, back & side wire




Rating W	Rating V/AC	Compatible lamp types	Description	Color suffix	Catalog no.
300	120	Dimmable LED/CFL	Decorator dimmer, single pole/3-way preset	C2, C4, C5, C6	<input type="checkbox"/> DAL06P-__
600	120	INC, HAL, FLR, MLV, ELV			
__	__	__	DAL06P Color change faceplate	B, BK, GY, LA, V, W	<input type="checkbox"/> DCK1-__

See instruction sheet for de-rating information

Color ordering information

For ordering devices, include Cat. no. followed by the color code: B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White), C2 (Color Change Kit - Light Almond, White, Ivory), C4 (Color Change Kit - Black, White, Ivory), C5 (Color Change Kit - Black, White, Gray), C6 (Color Change Kit - Oil Rubbed Bronze, White, Silver Granite)



Compliances, specifications and availability are subject to change without notice.

AL series dimmers



SAL06P3

Single pole and 3-way

- Adjustable low-end dim setting improves lamp compatibility
- Separate DIM/BRIGHT slider allows lights to be returned to favorite setting
- Large ON/OFF switch makes turning lights ON and OFF easy



SUT7

Single pole and 3-way

- Adjustable low-level trim setting for increased lamp compatibility
- Preset feature allows user to return to previous light level when turning lights ON
- Integrated full-slide control for easy, precise operation
- Dual rated for 120V/AC and 277V/AC. Suitable for commercial and residential applications

Slide AL series dimmers

Features

- Preset feature allows user to return to previous light level when turning lights ON
- Adjustable low-end dimming range
- Fixed Rapid Start provides quick power burst to ensure lights start even at low preset light levels
- No de-rating required in multi-gang installations



SAL06P3-W
(PJS26W wallplate sold separately)

Slide dimmers, back & side wire



Rating W	Rating V/AC	Compatible lamp Types	Description	Color suffix	Catalog no.
300	120	Dimmable LED/CFL	Slide dimmer, single pole/3-way preset	B, BK, GY, LA, V, W	□ SAL06P3-___
600	120	INC, HAL, FLR, MLV, ELV			



See instruction sheet for de-rating information

Universal slide dimmers (Forward Phase-Cut)

Features

- Universal dimming of most common dimmable lighting loads (phase-cut)
- Device can be wired into either 3-Way location (load side or line side)
- Neutral is not required for installation of devices
- Radio frequency interference filtering is standard on all models
- Electrostatic discharge protection
- Precise color matching



SUT7
(PJS26W wallplate sold separately)

Universal slide dimmers



Rating W	Rating V/AC	Compatible lamp Types	Description	Color suffix	Catalog no.
450	120	Dimmable LED/CFL/FLR	Universal slide dimmer, single pole/3-way preset	BK, GY, LA, V, W	□ SUT7-___
600	277				
720	120	INC, HAL, MLV, ELV			
1000	277				

Color ordering information

For ordering devices, include Cat. no. followed by the color code: B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)

B	BK	GY	LA	V	W
(Brown)	(Black)	(Gray)	(Lt. Almond)	(Ivory)	(White)

Compliances, specifications and availability are subject to change without notice.

Title 20/24 Compliant

AL series dimmers



TAL06P2

Single pole and 3-way

- Green LED locator light glows softly when lights are OFF
- Adjustable low-end dim setting improves lamp compatibility
- Separate DIM/BRIGHT bars allows lights to be returned to favorite settings
- Fully adjustable Rapid Start ensures the right amount of power boost during start-up

Color change faceplate options



TAL06P2
(PJS1W wallplate
sold separately)

Toggle AL series dimmers

Features

- Preset feature allows user to return to previous light level when turning lights ON
- Adjustable low-end dimming range
- Fully adjustable Rapid Start setting for optimal lamp start-up at low preset light levels
- No de-rating required in multi-gang installations
- Each color kit package includes 3 colors

Toggle dimmers, back & side wire



Rating W	V/AC	Compatible lamp types	Description	Color suffix	Catalog no.
300	120	Dimmable LED/CFL	Toggle dimmer, single pole/3-way preset	C2, C4, C5	<input type="checkbox"/> TAL06P2-___
600	120	INC, HAL, FLR, MLV, ELV			
___	___	___	TAL06P2 Color change faceplate	B, BK, GY, LA, V, W	<input type="checkbox"/> TCK3-___

See instruction sheet for de-rating information

Color ordering information

For ordering devices, include Cat. no. followed by the color code: B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White), C2 (Color Change Kit - Light Almond, White, Ivory), C4 (Color Change Kit - Black, White, Ivory), C5 (Color Change Kit - Black, White, Gray)

B (Brown)	BK (Black)	GY (Gray)	LA (Lt. Almond)	V (Ivory)	W (White)
LA	W	V	BK	W	V
C2 Color Kit (Light Almond, White, Ivory)			C4 Color Kit (Black, White, Ivory)		C5 Color Kit (Black, White, Gray)

Compliances, specifications and availability are subject to change without notice.

We make what matters work.*

* At Eaton, we believe that power is a fundamental part of just about everything people do. Technology, transportation, energy and infrastructure-these are things the world relies on every day. That's why Eaton is dedicated to helping our customers find new ways to manage electrical, hydraulic and mechanical power more efficiently, safely and sustainably. To improve people's lives, the communities where we live and work, and the planet our future generations depend upon. Because that's what really matters. And we're here to make sure it works.

See more at Eaton.com/whatmatters

Visit our website:
www.eaton.com/wiringdevices

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/wiringdevices

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2018 Eaton
All Rights Reserved
Printed in USA
Publication No. BR610032EN
August 2018

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/wiringdevices

Eaton is a registered trademark.
All other trademarks are property
of their respective owners.

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlan Km 17.8 s/n
Col. Villa Jardin esq.
Cerrada 8 de Mayo
Cuautitlan, Mexico CP 54800
Mexico
Eaton.mx
Eaton.com/wiringdevices

Follow us on social media to get the
latest product and support information.

