



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SBC3C Split Bolt Conn *Panduit Corporation*

|                  |   |
|------------------|---|
| Catalog Number   | SBC3C   |
| Manufacturer     | Panduit Corporation   |
| Description      | Split Bolt Connector, #8 Awg (Stranded) Conductor Size, #4 Awg (Stranded) Conductor Size, Non-Insulated, Copper Conductor Material, 1.16 In Overall Length, 1 LB/Ea |
| Weight per unit  | 1.0 (lbs/each)  |
| Product Category | Large Terminals & Connectors  |

### Features

|                |        |
|----------------|--------|
| Material       | Copper |
| media          | Yes    |
| Voltage Rating | 600 V  |

### Material, Color, and Finish

|        |          |
|--------|----------|
| Finish | Uncoated |
|--------|----------|

### Descriptions

|                        |  |
|------------------------|--|
| Also Known As...       | Bug<br>Kearnys<br>Split Bolt Connector<br>Monkey balls |
| Description            | SPLIT BOLT CONN  |
| extra long description | PAN SBC3-C Pan-Lug™ SBC3-C Mech Con                    |
| similar brands         | Servit®  |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | PANDUIT        |
| GTIN  | 00074983627226 |
| UPC   | 074983627226   |

### Taxonomies, Classifications, and Categories

|                      |                                 |
|----------------------|---------------------------------|
| Category Description | SPLIT BOLTS                     |
| Type                 | Mechanical Split Bolt Connector |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Package         | 100 |
| Weight Per each | 1   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

standard

UL listed to 467 and 486 and CSA certified for use up to 600V &  
Temperature Rated to 90°C

---