



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SBC8C Split Bolt Conn Panduit Corporation

Catalog Number	SBC8C
Manufacturer	Panduit Corporation
Description	Split Bolt Connector, #10 Awg (Stranded) Conductor Size, #8 Awg (Stranded) Conductor Size, Non-Insulated, Copper Conductor Material, 0.86 In Overall Length, 1 LB/Ea
Weight per unit	1.0 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Copper
media	Yes
Voltage Rating	600 V

### Material, Color, and Finish

Finish	blank
--------	-------

### Descriptions

Also Known As...	Kearnys Monkey balls Bug Split Bolt Connector
Description	SPLIT BOLT CONN
extra long description	PAN SBC8-C Pan-Lug™ SBC8-C Mech Con
similar brands	Servit®

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983904020
UPC	074983904020

### Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
Type	Mechanical Split Bolt Connector

### Packaging

Carton	1
Package	100
Weight Per each	1

### Uses, Certifications, and Standards

standard	UL listed to 467 and 486 and CSA certified for use up to 600V & Temperature Rated to 90°C
----------	---