



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SC4 #4 Cu Butt Splice

*Nsi Industries*

Catalog Number	SC4
Manufacturer	Nsi Industries
Description	Butt Splice Connector, #6 Awg Conductor Size, #4 Awg Conductor Size, Non-Insulated, Copper Conductor Material, Gray (Code) Insulation Color, 2 Conductors, +90 °C Operating Temperature, 1 In Overall Length, Compression Terminal, 600 V, 0.03 LB/Ea
Weight per unit	0.0300 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Copper
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Gray
Finish	Tin Plated

### Dimensions and Weight

Size	L=1.00 - OD=.340 - ID=.250
------	----------------------------

### Descriptions

Description	#4 CU BUTT SPLICE
extra long description	NSI SC-4 CU CMP Splice Short 350 MC
Features	StandardBarrel TinnedCopperSplice4 AWG Standard Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.

### Manufacturer Information

GTIN	00662381037022
UPC	662381037022

### Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - CU Splice

### Packaging

Carton	1
Package	100
Weight Per each	0.03



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)