


**CLIPS**  
**ELECTRICAL**

Featuring:



**Battery/Crocodile/General Purpose Test/Mini-Gator/Welding**



Style	Amp Rating	Material/Plating	Clip Jaws Open	Jaw Length	Wire Attachment	Use w/ Insulator #	Part Number*	Fig. No.
Battery	40	Steel/Zinc	3/4"	21/32"	Crimp/Screw	26	SC-25	1
Battery	50	Steel/Zinc	1-1/16"	25/32"	Crimp/Screw	23	SC-21A	2
Battery	50	Steel/Copper	1-1/8"	1"	Crimp/Solder	Insulated	SC-46A <sup>1</sup>	3
Battery	75	Copper	3/4"	21/32"	Crimp/Screw	26	SC-25C	1
Battery	75	Copper	1-1/8"	1"	Crimp/Solder	Insulated	SC-46C <sup>1</sup>	3
Battery	100	Steel/Zinc	1-5/8"	1"	Lug	13	SC-11A	4
Battery	100	Copper	1-1/16"	25/32"	Lug	23	SC-21C	2
Battery	200	Copper	1-5/8"	1"	Lug	13	SC-11C	4
Crocodile	5	Steel/Zinc	5/16"	15/16"	Crimp/Screw	87	SC-85	5
Crocodile	10	Copper	5/16"	15/16"	Crimp/Screw	87	SC-85C	5
General Purpose Test	10	Steel/Zinc	5/16"	1/4"	Crimp/Screw	47	SC-45	6
General Purpose Test	10	Steel/Zinc	7/16"	3/8"	Crimp/Screw	49	SC-55	7
General Purpose Test	10	Steel/Zinc	1/2"	3/8"	Crimp/Screw	49	SC-48B	8
General Purpose Test	20	Steel/Zinc	5/8"	17/32"	Crimp/Screw	29	SC-27 <sup>2</sup>	6
General Purpose Test	20	Copper	1/2"	3/8"	Crimp/Screw	49	SC-48C	8
General Purpose Test	40	Copper	5/8"	17/32"	Crimp/Screw	29	SC-27C <sup>2</sup>	6
Mini-Gator	5	Steel/Nickel	3/16"	7/16"	Crimp/Solder	32	SC-30	9
Mini-Gator	5	Copper	3/16"	7/16"	Crimp/Solder	32	SC-30C	9
Welding	300	Copper	1-13/16"	1-1/4"	Lug	35	SC-33C	10

\* Contact Sales Department for different types of packaging available.

1 Handles are insulated.

2 Length 2-7/16"

SELECTA SWITCH, INC. • Toll Free: 800-722-6445 • Toll Free Fax: 800-433-4319 • www.selectaswitch.com