



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## SCRS15TRSW Satin 15A Receptacle Tamper Resistant Snow

Lutron

Catalog Number	SCRS15TRSW
Manufacturer	Lutron
Description	Lutron Claro Tamper-Resistant Duplex Receptacle, 15 Amp, Snow
Weight per unit	0.3500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	15
connection	Screw Terminal
insulation	Plastic
Material	Plastic/Metal
Number of Wires	3,4,5
Poles	2
Voltage Rating	125
Wattage	1875
Wire Size	10 to 14

### Material, Color, and Finish

Color	SNOW
Finish	SATIN

### Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------

### Descriptions

Description	SATIN 15A RECEPTACLE TAMPER RESISTANT SNOW
extra long description	LUT SCRS-15-TR-SW SC 15A TAMPER RES
Features	Coordinate Lutron lighting controls and switches with Lutron Claro receptacles to complement your clients' decor. Install with screw terminals or push-in connections. Available in 7 Gloss colors and 20 Satin colors, Lutron receptacles become beautiful accessories that let you coordinate and customize the look of each room in any home. Pairs perfectly with Lutron Claro wall plates for consistent color matching (sold separately).
Long Description	Lutron Claro Tamper-Resistant Duplex Receptacle, 15 Amp, Snow
Product Type	SC 15A Tamper Resist Recp Snow
Special Features	Includes shutter mechanism (shutters are white). Wallplate sold separately.



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Lutron
GTIN	00027557618250
Manufacturers Part Number	SCRS-15-TR-SW
UPC	027557618250

## Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	Tamper-resistant receptacle

## Packaging

Carton	1
Package	24
Weight Per each	0.35

## Uses, Certifications, and Standards

environmental conditions	0 to 90% humidity, non-condensing
Mounting	WALLBOX
Temperature Rating	32 to 104