



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SDL615930D 120V, 60HZ, 15W, 0.125, CRI90, 30K, 992 White

Topaz - Southwire LLC

Catalog Number	SDL615930D
Manufacturer	Topaz - Southwire LLC
Description	Led Ceiling Mount Light Fixture, White Finish; 7.4 Inch; 15.5 Watt Wattage; Led Lamp Type; Rohs Compliant; Mounting Type Surface; Nominal Size 6 Inch; Voltage Rating 120 Volt; Beam Angle 35 Degree; Intensity 1050 Lumen; Color Rendering Index 90
Weight per unit	0.9000 (lbs/each)
Product Category	Led Surface Architectural & SP

Features

Lamp Type	LED
Wattage	15.5 Watt

Material, Color, and Finish

Finish	white
--------	-------

Dimensions and Weight

Width	7.4 Inch
-------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	RoHS Compliant; Mounting Type Surface; Nominal Size 6 Inch; Voltage Rating 120 Volt; Beam Angle 35 Degree; Intensity 1050 Lumen; Color Rendering Index 90; Color Temperature Rating 3000 Kelvin; Efficacy Rating 65 Lumen per Watt; Lamp Life 50000 Hour; Tempe
Commodity Description	LED SURFACE ARCHITECTURAL & SPECIFICATION LIGHTING
Description	120V,60HZ,15W,0.125,CRI90,30K,992 WHITE
extra long description	WHITE FINISH; 7.4 INCH; 15.5 WATT WATTAGE; LED LAMP TYPE; ROHS COMPLIANT; MOUNTING TYPE SURFACE; NOMINAL SIZE 6 INCH; VOLTAGE RATING 120 VOLT; BEAM ANGLE 35 DEGREE; INTENSITY 1050 LUMEN; COLOR RENDERING INDEX 90; COLOR TEMPERATURE RATING 3000 KELVIN; EFFICACY RATING 65 LUMEN PER WATT; LAMP LIFE 50000 HOUR; TEMPERATURE RATING -4 TO 104 DEG F; APPLICATION RESIDENTIAL, COMMERCIAL, DAMP AND WET LOCATION; APPROVAL UL; APPLICABLE STANDARD NEC 410.16 (A)(3)/(C)(5), TITLE 24, NFPA
Features	Topaz's 6 , 15 watt, 3000K, LED Surface Mount Disk Light with white finish are easy-to-install for new construction as well as retrofit applications and are designed to be mounted to most standard 4" J-boxes. Perfect for residential or commercial applications including bathrooms, closets, storage areas, hallways and living areas, they offer exceptional color rendering of 90 CRI and are dimmable down to 5% with standard incandescent or LED style leading edge dimmers. Their optical design provides a wide bea
Long Description	LED CEILING MOUNT LIGHT FIXTURE, WHITE FINISH; 7.4 INCH; 15.5 WATT WATTAGE; LED LAMP TYPE; ROHS COMPLIANT; MOUNTING TYPE SURFACE; NOMINAL SIZE 6 INCH; VOLTAGE RATING 120 VOLT; BEAM ANGLE 35 DEGREE; INTENSITY 1050 LUMEN; COLOR RENDERING INDEX 90
Product Type	Led Ceiling Mount Light Fixture

Manufacturer Information

Brand	TOPAZ
GTIN	00751338002753
Manufacturers Part Number	SDL6/15/930/D-28
UPC	751338002753

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
----------------------	--------------------------

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.9