

## Seoprene® 105 Black—Large Sizes



PART NUMBER	DESCRIPTION	STRANDING	NOMINAL INSULATION THICKNESS	NOMINAL JACKET THICKNESS	NOMINAL OD	AMPACITY	WT/M'
22320	8/3 SEOW	96/28	.048	.095	.700	40	282
22420	8/4 SEOW	96/28	.048	.100	.783	35	368
22470	8/5 SEOW	96/28	.048	.100	.850	28	442
22321	6/3 SEOW	96/26	.048	.100	.818	55	451
22421	6/4 SEOW	96/26	.048	.100	.892	45	573
22521	6/5 SEOW	96/26	.048	.110	.992	36	720
22322	4/3 SEOW	96/24	.048	.110	.982	70	668
22422	4/4 SEOW	96/24	.048	.125	1.104	60	882
22552	4/5 SEOW	96/24	.048	.125	1.203	48	1091
22323	2/3 SEOW	7 X 17/.0223	.050	.125	1.158	95	932
22423	2/4 SEOW	7 X 17/.0223	.050	.125	1.267	80	1152
22553	2/5 SEOW	7 X 17/.0223	.050	.135	1.389	64	1414

UL constructions available

**Applications:** Heavy machine tools; compressors; portable tools; robotics; motor controls.

## Suprene™ 105 Yellow

For use in the toughest environments. Offers a temperature rating of -60°C to 105°C and 25% more abrasion resistance. Use on heavy-duty industrial applications where chemicals and/or abrasion present a problem. Safety yellow color provides high visibility.



PART NUMBER	DESCRIPTION	STRANDING	NOMINAL INSULATION THICKNESS	NOMINAL JACKET THICKNESS	NOMINAL OD	AMPACITY	WT/M'
23345	18/3 SJEOOW	16/30	.031	.032	.318	10	52
23346	16/3 SJEOOW	26/30	.031	.032	.348	13	65
23446	16/4 SJEOOW	26/30	.031	.032	.376	10	76
23347	14/3 SJEOOW	41/30	.031	.032	.391	18	81
23447	14/4 SJEOOW	41/30	.031	.032	.418	15	103
23348	12/3 SJEOOW	65/30	.031	.047	.460	25	122
23349	10/3 SJEOOW	104/30	.031	.062	.599	30	216
22345	18/3 SEOW	16/30	.031	.062	.388	10	69
22445	18/4 SEOW	16/30	.031	.062	.407	7	78
22346	16/3 SEOW	26/30	.031	.062	.414	13	80
22446	16/4 SEOW	26/30	.031	.062	.446	10	96
22347	14/3 SEOW	41/30	.031	.082	.556	18	149
22447	14/4 SEOW	41/30	.031	.082	.591	15	180
22348	12/3 SEOW	65/30	.031	.097	.635	25	197
22448	12/4 SEOW	65/30	.031	.097	.674	20	240
22349	10/3 SEOW	104/30	.031	.095	.695	30	257
22449	10/4 SEOW	104/30	.031	.095	.735	25	313

**Applications:** Indoor and outdoor temporary power; wherever high visibility is needed for safety; high abrasion and chemical exposure.



**Seoprene®**

# Packaging Options

Coleman Cable offers four types of packaging options.


- Signa-Coil
- Reel-in-box
- Pull-out box (Rabbit pull)
- Reels

All provide fast and easy cable access. Kinks and twists are eliminated. You get tangle-free cable delivery each and every time. These durable, compact designs save on installation time while reducing waste and material costs. They can be easily stacked to save room.

\* Not all options are available for each product



## Coleman Cable Part Legend



Put-ups	Code
Reel, 250 ft	04
Reel, 500 ft	05
Reel, 1,000 ft	06
Reel-in-box, 1,000 ft	16
RabbitPull™ Pull-Box, 500 ft	45
RabbitPull™ Pull-Box, 1,000 ft	46
SignaCoil™ 500 ft	55
SignaCoil™ 1,000 ft	56

Colors	Code		Code
White	01	Pink	11
Yellow	02	Purple	13
Orange	03	Clear	18
Red	04	Fluorescent	
Green	05	Pink	21
Blue	06	Ivory	22
Brown	07	Natural	23
Black	08	Beige	33
Gray	09	Red Striped	
		CorraClad™	44



## Seoprene® 105 Black—Large Sizes



PART NUMBER	DESCRIPTION	STRANDING	NOMINAL INSULATION THICKNESS	NOMINAL JACKET THICKNESS	NOMINAL OD	AMPACITY	WT/M'
22320	8/3 SEOWW	96/28	.048	.095	.700	40	282
22420	8/4 SEOWW	96/28	.048	.100	.783	35	368
22470	8/5 SEOWW	96/28	.048	.100	.850	28	442
22321	6/3 SEOWW	96/26	.048	.100	.818	55	451
22421	6/4 SEOWW	96/26	.048	.100	.892	45	573
22521	6/5 SEOWW	96/26	.048	.110	.992	36	720
22322	4/3 SEOWW	96/24	.048	.110	.982	70	668
22422	4/4 SEOWW	96/24	.048	.125	1.104	60	882
22552	4/5 SEOWW	96/24	.048	.125	1.203	48	1091
22323	2/3 SEOWW	7 X 17/.0223	.050	.125	1.158	95	932
22423	2/4 SEOWW	7 X 17/.0223	.050	.125	1.267	80	1152
22553	2/5 SEOWW	7 X 17/.0223	.050	.135	1.389	64	1414

UL constructions available

**Applications:** Heavy machine tools; compressors; portable tools; robotics; motor controls.

## Suprene™ 105 Yellow

For use in the toughest environments. Offers a temperature rating of -60°C to 105°C and 25% more abrasion resistance. Use on heavy-duty industrial applications where chemicals and/or abrasion present a problem. Safety yellow color provides high visibility.



PART NUMBER	DESCRIPTION	STRANDING	NOMINAL INSULATION THICKNESS	NOMINAL JACKET THICKNESS	NOMINAL OD	AMPACITY	WT/M'
23345	18/3 SJEOOW	16/30	.031	.032	.318	10	52
23346	16/3 SJEOOW	26/30	.031	.032	.348	13	65
23446	16/4 SJEOOW	26/30	.031	.032	.376	10	76
23347	14/3 SJEOOW	41/30	.031	.032	.391	18	81
23447	14/4 SJEOOW	41/30	.031	.032	.418	15	103
23348	12/3 SJEOOW	65/30	.031	.047	.460	25	122
23349	10/3 SJEOOW	104/30	.031	.062	.599	30	216
22345	18/3 SEOWW	16/30	.031	.062	.388	10	69
22445	18/4 SEOWW	16/30	.031	.062	.407	7	78
22346	16/3 SEOWW	26/30	.031	.062	.414	13	80
22446	16/4 SEOWW	26/30	.031	.062	.446	10	96
22347	14/3 SEOWW	41/30	.031	.082	.556	18	149
22447	14/4 SEOWW	41/30	.031	.082	.591	15	180
22348	12/3 SEOWW	65/30	.031	.097	.635	25	197
22448	12/4 SEOWW	65/30	.031	.097	.674	20	240
22349	10/3 SEOWW	104/30	.031	.095	.695	30	257
22449	10/4 SEOWW	104/30	.031	.095	.735	25	313

**Applications:** Indoor and outdoor temporary power; wherever high visibility is needed for safety; high abrasion and chemical exposure.



**Seoprene®**

# Packaging Options

Coleman Cable offers four types of packaging options.


- Signa-Coil
- Reel-in-box
- Pull-out box (Rabbit pull)
- Reels

All provide fast and easy cable access. Kinks and twists are eliminated. You get tangle-free cable delivery each and every time. These durable, compact designs save on installation time while reducing waste and material costs. They can be easily stacked to save room.

\* Not all options are available for each product



## Coleman Cable Part Legend



Put-ups	Code	Colors	Code
Reel, 250 ft	04	White	01
Reel, 500 ft	05	Yellow	02
Reel, 1,000 ft	06	Orange	03
Reel-in-box, 1,000 ft	16	Red	04
RabbitPull™ Pull-Box, 500 ft	45	Green	05
RabbitPull™ Pull-Box, 1,000 ft	46	Blue	06
SignaCoil™ 500 ft	55	Brown	07
SignaCoil™ 1,000 ft	56	Black	08
		Gray	09
		Pink	11
		Purple	13
		Clear	18
		Fluorescent	
		Pink	21
		Ivory	22
		Natural	23
		Beige	33
		Red Striped	
		CorraClad™	44

