



Powering Business Worldwide

pe.eaton.com

Dimmer

SF10P-W

UPC:032664736926

Dimensions:

- **Height:** 4.3 IN
- **Length:** 2 IN
- **Width:** 2 IN

Weight:.23 LB

Warranties: No Data

Specifications:

- **Special Features:** No neutral required
- **Allowable Wire Size:** #14 -12 AWG
- **Mounting Type:** Flush
- **Voltage Rating:** 120/277V
- **Wiring Method:** Back and side, Wire Leads
- **Closure Type:** Maintained
- **Color:** White
- **Frequency Rating:** 60 Hz
- **Load Type:** LED, Fluorescent
- **Number Of Poles:** Single-pole
- **Number of Ways:** Three-way
- **Phase:** Single-phase
- **Material:** Polycarbonate
- **Wattage:** 1200/1660W

Supporting documents: No Data

Certifications:

- cULus Listed
- NOM

Product compliance: No Data

