

# Eaton SFBCVR225BBOT

Catalog Number: SFBCVR225BBOT

Eaton Pow-R-Xpress 225A MAX SFB CVR FOR 600A PNL BOT

## General specifications




Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Pow-R-Xpress subfeed cover	SFBCVR225BBOT
<b>UPC</b>	<b>Product Length/Depth</b>
786689397258	23 in
<b>Product Height</b>	<b>Product Width</b>
0.1 in	11 in
<b>Product Weight</b>	<b>Compliances</b>
2 lb	NEMA Compliant
<b>Certifications</b>	
UL 67	

## Physical Attributes

### Type

SFB CVR 600A PNL BOT

## Resources

### Brochures

[Pow-R-Xpress quick selector reference guide](#)

[Pow-R-Xpress stocking program flyer](#)

[Eaton's Pow-R-Xpress stocking program](#)

### Installation instructions

[PRL1X Or PRL2X Panelboard Instructions](#)

### Multimedia

[Pow-R-Line Xpert family overview](#)

### Specifications and datasheets

[Eaton Specification Sheet - SFBCVR225BBOT](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)