



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SG3A0225KB D16 SNTL-G 3PH 225KVA 480D-208Y/120V AI 60HZ 150C *Hammond Power Solutions*

Catalog Number	SG3A0225KB
Manufacturer	Hammond Power Solutions
Description	600V Class Three Phase DOE2016 and Nrcan 2019 Compliant Energy Efficient Distribution Transformer, 480D PV, 208Y/120 SV, 225 Kva, 3PH, Aluminum Wound
Weight per unit	1,350.0 (lbs/each)
Product Category	Three Phase Energy Efficient D

Features

kva rating	225
Number of Phases	3
Number of Taps	ST-20 compliant
Phase	A - 3PH Delta-Wye-N
Primary Voltage	480D
Secondary Voltage	208Y/120

Dimensions and Weight

Height	52
Length	34
Width	37.5

Descriptions

Description	D16 SNTL-G 3PH 225KVA 480D-208Y/120V AL 60HZ 150C
extra long description	HMND SG3A0225KB D16/NRC19 3PH 225kV
Features	Optional infrared windows available
Long Description	600V Class Three Phase DOE2016 and NRCan 2019 Compliant Energy Efficient Distribution Transformer, 480D PV, 208Y/120 SV, 225 kVA, 3PH, Aluminum Wound
Product Type	D16/NRC19 3PH 225KVA 480D-208Y/120V AI
Special Features	Meets current DOE 10 CFR part 431 (2016) and C802.2 efficiencies in an outdoor type enclosure. Smaller kVA sizes have standard input and/or output lugs, knockouts, and wall mounting brackets to save installation costs.

Manufacturer Information

Brand	HPS
GTIN	00803423121976
Manufacturers Part Number	SG3A0225KB
UPC	803423121976



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	3 PHASE TRANSFORMERS
Type	Transformer > Distribution > DOE 2016 Energy Efficient > General Purpose > Three Phase

Packaging

Carton	1
Weight Per each	1350

Uses, Certifications, and Standards

Application	General purpose for supplying appliance, lighting, motorized machine and power loads from electrical distribution systems.
Enclosure	DH5-N3R - Indoor or Outdoor
Frequency Rating	60
Mounting standard	Floor Mount CSA, UL
Temperature Rating	Typical 30 Average/ 40 Maximum