



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SG3N0025LE D16 SNTL-G3 1PH 25KVA 240X480-120/240V AI 60HZ 150 *Hammond Power Solutions*

Catalog Number	SG3N0025LE
Manufacturer	Hammond Power Solutions
Description	600V Class Single Phase DOE2016 and Nrcan 2019 Compliant Energy Efficient Distribution Transformer, 240X480 PV, 120/240 SV, 25 Kva, 1PH, Aluminum Wound
Weight per unit	210.0 (lbs/each)
Product Category	20170612135628

### Features

kva rating	25
Number of Taps	ST-20 compliant
Phase	N- 1PH Dual-Dual
Primary Voltage	240x480
Secondary Voltage	120/240

### Dimensions and Weight

Height	26.7
Length	23.8
Width	22.3

### Descriptions

Description	D16 SNTL-G3 1PH 25KVA 240X480-120/240V AL 60HZ 150
extra long description	HMND SG3N0025LE D16/NRC19 1PH 25kVA
Features	Optional infrared windows available
Long Description	600V Class Single Phase DOE2016 and NRCan 2019 Compliant Energy Efficient Distribution Transformer, 240x480 PV, 120/240 SV, 25 kVA, 1PH, Aluminum Wound
Product Type	D16/NRC19 1PH 25KVA 240X480 120/240val
Special Features	Meets current DOE 10 CFR part 431 (2016) and C802.2 efficiencies in an outdoor type enclosure. Smaller kVA sizes have standard input and/or output lugs, knockouts, and wall mounting brackets to save installation costs.

### Manufacturer Information

Brand	HPS
GTIN	00803423140649
Manufacturers Part Number	SG3N0025LE
UPC	803423140649



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	1 PHASE TRANSFORMERS
Type	Transformer > Distribution > DOE 2016 Energy Efficient > General Purpose > Single Phase

## Packaging

Carton	1
Weight Per each	210

## Uses, Certifications, and Standards

Application	General purpose for supplying appliance, lighting, motorized machine and power loads from electrical distribution systems.
Enclosure	NH6-N3R - Indoor or Outdoor
Frequency Rating	60
Mounting standard	Floor or Wall mount CSA, UL
Temperature Rating	Typical 30 Average/ 40 Maximum