



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SGABM25AC 1X1" WHT Super Grip CBL Tie MNT

*Panduit Corporation*

Catalog Number	SGABM25AC
Manufacturer	Panduit Corporation
Description	The Panduit SGABM25-A-C Super Grip Rubber Adhesive Backed Cable Tie Mounts Are Made Of Nylon 6.6 and Are For Use With Miniature and Intermediate Cross-Section Super-Grip Cable Ties. Designed For Indoor Use, Especially In Areas Where Space Is Limited. They Measure 1.0" X 1.0" (25.4MM X 25.4MM), Supplied In Strips Of 2, Are White In Color and Come In Packages Of 100.
Weight per unit	0.3700 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

Cable Size	NA
Cable Type	Cable Tie Mount
insulation	Other
Material	Nylon 6.6
media	Yes

### Material, Color, and Finish

Color	White
-------	-------

### Descriptions

Description	1X1" WHT SUPER GRIP CBL TIE MNT
extra long description	PAN SGABM25-A-C Super-Grip® SGABM25
Long Description	The Panduit SGABM25-A-C super grip rubber adhesive backed cable tie mounts are made of Nylon 6.6 and are for use with miniature and intermediate cross-section Super-Grip cable ties. Designed for indoor use, especially in areas where space is limited. They measure 1.0" x 1.0" (25.4mm x 25.4mm), supplied in strips of 2, are white in color and come in packages of 100.
Product Type	Super-Grip® SGABM25-A-C Super-Grip™ Mount, White, Pa 6.6, Ru

### Manufacturer Information

Brand	PANDUIT
GTIN	00074983526802
Manufacturers Part Number	SGABM25-A-C
UPC	074983526802

### Taxonomies, Classifications, and Categories

Type	Cable Tie Mount
------	-----------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	100
Package	500
Weight Per each	0.37

## Uses, Certifications, and Standards

Application	Indoor
Mounting	Adhesive Tape
Operating Temperature	120
standard	CE Compliant, RoHS Compliant