



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SGB384CL 1-1/4" Diecast Mighty-Right Split Ground Bushing

*Bridgeport Fittings*

Catalog Number	SGB384CL
Manufacturer	Bridgeport Fittings
Description	Split Bushing, Insulated, Grounding, Zinc Die Cast, Size 1-1/4 Inch, 14-1/0 Lug
Weight per unit	0.2910 (lbs/each)
Product Category	Aluminum

### Features

Material	Zinc Alloy
media	Yes

### Material, Color, and Finish

Color	Grey with Black Insulator
Finish	Ball burnish

### Dimensions and Weight

Size	1-1/4
------	-------

### Descriptions

Description	1-1/4" DIECAST MIGHTY-RIGHT SPLIT GROUND BUSHING
extra long description	BPT SGB-384CL 1-1/4" SPLT GND BSH #
Features	Split Bushings install after the wire pull. No more burning through bushings or fighting with pullers. Save time and effort too!
Long Description	Split Bushing, Insulated, Grounding, Zinc Die Cast, Size 1-1/4 Inch, 14-1/0 Lug
Product Type	1-1/4" SPLT GND BSH #14-1/0awg
Special Features	Grounding Lug Wire Capacity # 14 - #4

### Manufacturer Information

Brand	Bridgeport Fittings
GTIN	00781747903846
Manufacturers Part Number	SGB-384CL
UPC	781747903846

### Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	SPLIT

### Trade Size

Trade Size	1.25
------------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	20
Package	200
Weight Per each	0.291

## Uses, Certifications, and Standards

Application	Used in situations where wires have already been pulled through Rigid/IMC conduit, and an insulated bushing is required. Grounding lug; aluminum alloy 6061-T6. Rated 150 Degree C. cULus listed. Patented. Now featuring UV Stabilized Insulators and Stainless Steel Hardware, perfect for solar and other outdoor installations!
standard	cULus
Temperature Rating	150°C