



Powering Business Worldwide

pe.eaton.com

Arrow Hart Specification Grade GFCI Receptacle

SGF15W-M

UPC:032664742453

Dimensions:

- **Height:** 4.901 IN
- **Length:** 1.68 IN
- **Width:** 3.124 IN

Weight:.36 LB

Warranties: No Data

Specifications:

- **Type:** Mid-size
- **Amperage Rating:** 15A
- **Voltage Rating:** 125V
- **Wiring Method:** Back wire and side wire
- **Circuit Interrupter Type:** GFCI
- **Color:** White
- **Contact Material:** Brass
- **Device Type:** Receptacle
- **Face/Body Material:** PVC
- **Nema Configuration:** 5-15R
- **Receptacle Type:** Two-pole, three-wire, grounding

Supporting documents: No Data

Certifications:

- cULus Listed
- NOM

Product compliance: No Data





Powering Business Worldwide

pe.eaton.com

Arrow Hart Specification Grade GFCI Receptacle

SGF15W-M

UPC:032664742453

Dimensions:

- **Height:** 4.901 IN
- **Length:** 1.68 IN
- **Width:** 3.124 IN

Weight:.36 LB

Warranties: No Data

Specifications:

- **Type:** Mid-size
- **Amperage Rating:** 15A
- **Voltage Rating:** 125V
- **Wiring Method:** Back wire and side wire
- **Circuit Interrupter Type:** GFCI
- **Color:** White
- **Contact Material:** Brass
- **Device Type:** Receptacle
- **Face/Body Material:** PVC
- **Nema Configuration:** 5-15R
- **Receptacle Type:** Two-pole, three-wire, grounding

Supporting documents: No Data

Certifications:

- cULus Listed
- NOM

Product compliance: No Data

