


Specification grade GFCIs

Specification grade ground fault circuit interrupter receptacles

Product description












2-pole, 3-wire grounding
15A, 125V/AC; 20A, 125V/AC
NEMA 5-15, 5-20



5-15R

5-20R

Specification grade GFCIs

| Rating | | A | V/AC | NEMA | Description | Color suffix | Catalog no. |  |  |  |
|--------|-----|-------|------|------|---|----------------------------|------------------------------------|---|---|---|
| 15 | 125 | 5-15R | | | Duplex GFCI, back & side wire | A, B, BK, GY, LA, V, W | <input type="checkbox"/> SGF15__ |  | | |
| | | | | | Duplex GFCI, mid-size wallplate, back & side wire | A, LA, V, W | <input type="checkbox"/> SGF15__-M | | | |
| | | | | | Duplex GFCI, back & side wire | B, BK, GY, LA, RD, V, W | <input type="checkbox"/> SGF15F__ |  |  |  |
| 20 | 125 | 5-20R | | | Duplex GFCI, back & side wire | A, B, BK, GY, LA, RD, V, W | <input type="checkbox"/> SGF20__ |  | | |
| | | | | | Duplex GFCI, back & side wire | B, BK, GY, LA, RD, V, W | <input type="checkbox"/> SGF20F__ |  |  |  |

Includes standard size unbreakable wallplate unless otherwise noted
Consult factory customer service representative for additional packaging options








Specification grade combination GFCI receptacle & switch


| Rating | | A | V/AC | NEMA | Description | Color suffix | Catalog no. |
|--------|-----|-------|------|------|--|--------------|---------------------------------------|
| 15 | 125 | 5-15R | | | GFCI receptacle with feed-through single-pole switch (rated 1800W @ 120V/AC, 60Hz) | A, LA, V, W | <input type="checkbox"/> SGFS15__-MSP |

Specification grade blank face GFCI


| Rating | | A | V/AC | Description | Color suffix | Catalog no. |
|--------|-----|---|------|---|-----------------|-----------------------------------|
| 20 | 125 | | | Blank face (dead front) GFCI, rated as 1.5HP motor control switch, back & side wire | A, BK, LA, V, W | <input type="checkbox"/> SGFD20__ |

Accessories for GFCIs


| Description | Color suffix | Catalog no. |  |  |
|---|---------------|----------------------------------|---|---|
| GFCI 7/8" extension ring, cULus Listed | BLK, LA, V, W | <input type="checkbox"/> GFER__ |  | |
| Metal self-closing horizontal 1-Gang weather protective cover, decorator opening | | <input type="checkbox"/> S1966 |  |  |
| While-in-use metal weather protective standard depth 1-Gang cover, vertical mount | | <input type="checkbox"/> WIUMV-1 |  |  |



SGF15



SGFS15



SGFD20



GFER



S1966



WIUMV-1



WIUMH-1


Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White)

| | | | | | | | |
|----------|----------|---------------|-----------|--------------|-----------|----------|----------|
| A | B | BK/BLK | GY | LA | RD | V | W |
| (Almond) | (Brown) | (Black) | (Gray) | (Lt. Almond) | (Red) | (Ivory) | (White) |

Specification information: Specification grade GFCI: H-18

Compliances, specifications and availability are subject to change without notice.

 ArrowLink option available. Add "MOD" suffix to standard catalog number (example SGF15W, SGF15WMOD). For ordering information on ArrowLink & ArrowLink SPD connectors, see Page H-4



 RoHS compliant - Page Q-32

Specification grade GFCIs

Specification grade ground fault circuit interrupter receptacles

Product description

2-pole, 3-wire grounding
15A, 125V/AC; 20A, 125V/AC
NEMA 5-15, 5-20



5-15R



5-20R

Specification grade GFCIs



| Rating | | A | V/AC | NEMA | Description | Color suffix | Catalog no. | |
|--------|-----|-------|------|-------|---|----------------------------|------------------------------------|-------|
| 15 | 125 | 5-15R | 125 | 5-15R | Duplex GFCI, back & side wire | A, B, BK, GY, LA, V, W | <input type="checkbox"/> SGF15__ | • |
| | | | | | Duplex GFCI, mid-size wallplate, back & side wire | A, LA, V, W | <input type="checkbox"/> SGF15__-M | |
| | | | | | Duplex GFCI, back & side wire | B, BK, GY, LA, RD, V, W | <input type="checkbox"/> SGF15F__ | • • • |
| 20 | 125 | 5-20R | 125 | 5-20R | Duplex GFCI, back & side wire | A, B, BK, GY, LA, RD, V, W | <input type="checkbox"/> SGF20__ | • |
| | | | | | Duplex GFCI, back & side wire | B, BK, GY, LA, RD, V, W | <input type="checkbox"/> SGF20F__ | • • • |

Includes standard size unbreakable wallplate unless otherwise noted
Consult factory customer service representative for additional packaging options

Specification grade combination GFCI receptacle & switch



| Rating | | A | V/AC | NEMA | Description | Color suffix | Catalog no. |
|--------|-----|-------|------|-------|--|--------------|---------------------------------------|
| 15 | 125 | 5-15R | 125 | 5-15R | GFCI receptacle with feed-through single-pole switch (rated 1800W @ 120V/AC, 60Hz) | A, LA, V, W | <input type="checkbox"/> SGFS15__-MSP |


Specification grade blank face GFCI




| Rating | | A | V/AC | Description | Color suffix | Catalog no. |
|--------|-----|---|------|---|-----------------|-----------------------------------|
| 20 | 125 | | 125 | Blank face (dead front) GFCI, rated as 1.5HP motor control switch, back & side wire | A, BK, LA, V, W | <input type="checkbox"/> SGFD20__ |

Accessories for GFCIs


| Description | Color suffix | Catalog no. | |
|---|---------------|----------------------------------|-----|
| GFCI 7/8" extension ring, cULus Listed | BLK, LA, V, W | <input type="checkbox"/> GFER__ | • |
| Metal self-closing horizontal 1-Gang weather protective cover, decorator opening | | <input type="checkbox"/> S1966 | • • |
| While-in-use metal weather protective standard depth 1-Gang cover, vertical mount | | <input type="checkbox"/> WIUMV-1 | • • |



SGF15



SGFS15



SGFD20



GFER



S1966



WIUMV-1



WIUMH-1

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White)

| | | | | | | | |
|----------|---------|---------|--------|--------------|-------|---------|---------|
| A | B | BK/BLK | GY | LA | RD | V | W |
| (Almond) | (Brown) | (Black) | (Gray) | (Lt. Almond) | (Red) | (Ivory) | (White) |

Specification information: Specification grade GFCI: H-18

Compliances, specifications and availability are subject to change without notice.

➤ ArrowLink option available. Add "MOD" suffix to standard catalog number (example SGF15W, SGF15WMOD). For ordering information on ArrowLink & ArrowLink SPD connectors, see Page H-4



RoHS compliant - Page Q-32