

Specifications



Photo is representative



Eaton SGFS15V-MSP

Eaton GFCI receptacle, 120 V Self-Test GFCI recept, Decorator compatible, #14 - #12 AWG, 15A, Commer, 125V, bk and sd wiring, togg, Maint closure, Ivy, Mid-size walplt, 60 Hz, 5-15R, -35-66°C, 1-pole, thermoplas, PVC, 1800W

General specifications

PRODUCT NAME	Eaton GFCI receptacle
CATALOG NUMBER	SGFS15V-MSP
UPC	032664750083
PRODUCT LENGTH/DEPTH	1.68 in
PRODUCT HEIGHT	4.2 in
PRODUCT WIDTH	1.26 in
PRODUCT WEIGHT	0.001 lb
CERTIFICATIONS	NOM cULus Listed



Powering Business Worldwide

Product specifications

TYPE	Decorator compatible
AMPERAGE RATING	15A
VOLTAGE RATING	125 V
FEATURES	Mid-size wallplate Combination with switch
APPLICATION	Commercial
DEVICE GRADE	Commercial
WIRING METHOD	Back and side
TORQUE RATING	16 lbf-inch
MOUNTING METHOD	Flush

Resources

BROCHURES	GFCI brochure
INSTALLATION INSTRUCTIONS	Installing and testing a GFCI receptacle instruction sheet
MULTIMEDIA	What is a Ground Fault Circuit Interrupting (GFCI) receptacle?
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - SGFS15V-MSP

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

