



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SKAB250 250MCM Al/Cu Butt Splice

Nsi Industries

Catalog Number	SKAB250
Manufacturer	Nsi Industries
Description	Easy-Splice Dual Rated Direct Burial Butt Splice Kit For 1/0 Awg to 250 MCM Utilizing A Mechanical Dual Rated Splice and Matched Heavy Wall Heat Shrink Tubing to Create An Insulated Splice For Copper and/or Aluminum Cables. Temperature Rating: 105 Degrees C. 600 Volt Maximum.
Weight per unit	0.3760 (lbs/each)
Product Category	Splicing & Terminating Kits

Features

Cable Size	1/0 AWG-250 MCM
Cable Type	Class A-B
insulation	Heat Shrink
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Black
-------	-------

Descriptions

Description	250MCM AL/CU BUTT SPLICE
extra long description	NSI SKAB-250 Easy Splice ALCU Butt
Features	Easy-Splice Dual Rated Direct Burial Butt Splice Kit for 1/0 AWG to 250 MCM Utilizing a mechanical dual rated splice and matched heavy wall heat shrink tubing to create an insulated splice for copper and/or aluminum cables. Temperature Rating: 105 degrees C. 600 Volt Maximum.
Long Description	Easy-Splice Dual Rated Direct Burial Butt Splice Kit for 1/0 AWG to 250 MCM Utilizing a mechanical dual rated splice and matched heavy wall heat shrink tubing to create an insulated splice for copper and/or aluminum cables. Temperature Rating: 105 degrees C. 600 Volt Maximum.
Product Type	Easy Splice Alcu Butt Splice 250
Special Features	Dual Rated For Use With Copper And Aluminum Cable

Manufacturer Information

Brand	NSi
GTIN	00662381169167
Manufacturers Part Number	SKAB-250
UPC	662381169167

Taxonomies, Classifications, and Categories

Type	Direct Burial Splice Kit With Heat Shrink
------	---



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.376

Uses, Certifications, and Standards

Application	Splicing Wire
Operating Temperature	-40 C To 90 C