

SL2531 -- Air Tool Oil, 15 Fl Oz



### Product Description

A special lubricant designed for pneumatic equipment and tools.

### Product Specifications

<b>Applications</b>	Impact wrenches, air ratchets, sanders, grinders, air motors, hammers, drills, etc.
<b>Unit Package Description</b>	15 Ounce Bottle
<b>Brand</b>	Sta-Lube
<b>Generic Description 1</b>	Air Tool Oil
<b>Net Fill</b>	15 Fl Oz
<b>UPC Code</b>	0 72213 25310 8
<b>Unit Dimensions-Inches</b>	9H x 1.63W x 3.75D
<b>Units Per Case</b>	12
<b>Case Dimensions-Inches</b>	9.75H x 8.5W x 11.5D
<b>Cases Per Pallet</b>	133
<b>Lbs. Per Case</b>	13
<b>I 2 of 5 Code</b>	30072213253109
<b>Appearance</b>	Amber Viscous Liquid
<b>Odor</b>	Faint Petroleum
<b>Flashpoint - TCC Method</b>	>300°F
<b>Specific Gravity</b>	0.91
<b>Flammability</b>	Non-flammable
<b>Plastic Safe</b>	Yes
<b>Evaporation Rate</b>	<1 (butyl acetate=1)
<b>ISO Viscosity Grade</b>	22
<b>Working Temp [Degrees F]</b>	-20 to 225°F
<b>DOT Proper Shipping Name</b>	Not Regulated
<b>VOC % (Federal)</b>	0
<b>VOC g/L (Federal)</b>	0
<b>VOC Lbs./Gal. (Federal)</b>	0
<b>VOC Compliant For CA</b>	Not Regulated
<b>VOC Compliant For OTC/LADCO</b>	Not Regulated
<b>VOC Category/Limit</b>	Not Regulated

SL2531 -- Air Tool Oil, 15 Fl Oz



### Product Description

A special lubricant designed for pneumatic equipment and tools.

### Product Specifications

<b>Applications</b>	Impact wrenches, air ratchets, sanders, grinders, air motors, hammers, drills, etc.
<b>Unit Package Description</b>	15 Ounce Bottle
<b>Brand</b>	Sta-Lube
<b>Generic Description 1</b>	Air Tool Oil
<b>Net Fill</b>	15 Fl Oz
<b>UPC Code</b>	0 72213 25310 8
<b>Unit Dimensions-Inches</b>	9H x 1.63W x 3.75D
<b>Units Per Case</b>	12
<b>Case Dimensions-Inches</b>	9.75H x 8.5W x 11.5D
<b>Cases Per Pallet</b>	133
<b>Lbs. Per Case</b>	13
<b>I 2 of 5 Code</b>	30072213253109
<b>Appearance</b>	Amber Viscous Liquid
<b>Odor</b>	Faint Petroleum
<b>Flashpoint - TCC Method</b>	>300°F
<b>Specific Gravity</b>	0.91
<b>Flammability</b>	Non-flammable
<b>Plastic Safe</b>	Yes
<b>Evaporation Rate</b>	<1 (butyl acetate=1)
<b>ISO Viscosity Grade</b>	22
<b>Working Temp [Degrees F]</b>	-20 to 225°F
<b>DOT Proper Shipping Name</b>	Not Regulated
<b>VOC % (Federal)</b>	0
<b>VOC g/L (Federal)</b>	0
<b>VOC Lbs./Gal. (Federal)</b>	0
<b>VOC Compliant For CA</b>	Not Regulated
<b>VOC Compliant For OTC/LADCO</b>	Not Regulated
<b>VOC Category/Limit</b>	Not Regulated