



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SMCBL122BRGY 12/2 WG MC Sol BR/Gy/GN Steel Armor 250' *Southwire Company*

Catalog Number	SMCBL122BRGY
Manufacturer	Southwire Company
Description	Metal Clad Cable, Solid, #12 Awg Conductor Size, PVC Jacket Material, Thermoplastic Insulation Material, Copper Conductor Material, 600 V, 20 A, Gray, Brown and Green, 2 Conductors, 250 FT Overall Length, 0.475 In Outside Diameter, +90 °C Operating Temperature, 142 LB/MFT
Weight per unit	0.1050 (lbs/ft)
Product Category	Steel Armor Copper Conductors

Features

media	Yes
-------	-----

Dimensions and Weight

Length	250
--------	-----

Descriptions

Description	12/2 WG MC SOL BR/GY/GN STEEL ARMOR 250'
extra long description	SWC 57109801 Blue Steel Armor Type

Manufacturer Information

GTIN	00032886875588
UPC	032886875588

Taxonomies, Classifications, and Categories

Category Description	BX & MC
Type	MC

Availability

minimum qty	250
-------------	-----

Packaging

Carton	250
Weight Per foot	0.105