



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SMIC0105AC 120V Ac/DC Smoke/CO Combo 10 Yr Life - UL 217 8TH

BRK Brands/Ademco/First Alert

Catalog Number	SMIC0105AC
Manufacturer	BRK Brands/Ademco/First Alert
Description	Hardwired Combo Smoke & CO Alarm With 10-Year Locked 9V Lithium Battery Backup. Ac 120V Interconnectable With Silence and Latching Features. Includes Ionization Smoke Sensing Technology and Electrochemical Carbon Monoxide Sensor.
Weight per unit	0.7000 (lbs/each)
Product Category	Builders Products

Features

dimensions	2.25 in 5.69 in 5.69 in
------------	-------------------------

Material, Color, and Finish

Color	White
-------	-------

Descriptions

Description	120V AC/DC SMOKE/CO COMBO 10 YR LIFE - UL 217 8TH
extra long description	BRK 1046884 Smoke and CO Alarm
Features	Combo Smoke and CO Alarm
Long Description	Hardwired Combo smoke & CO alarm with 10-Year locked 9V lithium battery backup. AC 120V Interconnectable with Silence and Latching features. Includes Ionization smoke sensing technology and electrochemical carbon monoxide sensor.
Product Type	Alarm Combo Ac/DC10 SMICO105-Ac Box
Short Description	Combo Smoke and CO Alarm
Special Features	End-of-Life Warning,Battery Backup,Hardwire Interconnectivity,Hardwire Quick Connect Plug Included,Precision Detection

Manufacturer Information

Brand	BRK
GTIN	00029054022677
Manufacturers Part Number	SMICO105-AC
UPC	029054022677

Taxonomies, Classifications, and Categories

Category Description	SMOKE DETECTORS
Type	Combination Smoke & Carbon Monoxide Alarm

Packaging

Carton	1
Package	12
Weight Per each	0.7



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application
standard

Precision Detection

Conforms to UL 217 8th Edition Standard, Conforms to STD
UL2034