



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SNG6 6" Snaggletooth Pro Saw

L.H. Dottie CO.

Catalog Number	SNG6
Manufacturer	L.H. Dottie CO.
Description	Snaggle Tooth Pro Saw, 12 In. Overall Length, 6 In. Blade Length, Laser Cut Triple Ground Teeth Type, Triangular Handle Type
Weight per unit	0.3500 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

Features

Blade Length	6
Handle Type	Triangular
Teeth Type	Laser Cut Triple Ground

Dimensions and Weight

Overall Length	12
----------------	----

Descriptions

Description	6" SNAGGLETOOTH PRO SAW
extra long description	DOTTIE SNG6 6" Snaggletooth Pro Saw
Long Description	Snaggle Tooth Pro Saw, 12 in. overall length, 6 in. blade length, Laser Cut Triple Ground teeth type, Triangular handle type
Product Type	6" Snaggletooth Pro Saw
Special Features	Features: Easily Cuts Wallboard, Drywall, Plywood, Plastic, Blade Cuts in Both Directions, Laser Cut Triple Ground Teeth, Triangular Handle, Sheeth Included

Manufacturer Information

Brand	LH DOTTIE
GTIN	00781002420927
Manufacturers Part Number	SNG6
UPC	781002420927

Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
Type	Snaggle Tooth Pro Saw

Packaging

Carton	1
Weight Per each	0.35

Uses, Certifications, and Standards

Application	For Cutting Openings For Electrical Outlets
-------------	---