



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SP23LA Wallplate 2G Blank La *Pass & Seymour/Legrand*

| | |
|------------------|---|
| Catalog Number | SP23LA |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Plate Plastic 2-Gang Blank Without Line |
| Weight per unit | 0.1459 (lbs/each) |
| Product Category | Wall Plates & Covers |

Features

| | |
|-----------------|-------------|
| cutout | Blank |
| indoor/outdoor | Indoor |
| insulation | Bare |
| Mounting Type | Box Mounted |
| Number of Gangs | 2 |
| orientation | Vertical |
| Wall Plate Type | Blank |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|-----------|------|
| Size | 5" |
| Thickness | 0.07 |

Descriptions

| | |
|------------------------|---|
| Construction | Plastic |
| Description | WALLPLATE 2G BLANK LA |
| extra long description | P&S SP23LA WALL PLATE 2G BLANK LIGH |
| Long Description | Plate Plastic 2-Gang Blank Without Line |
| Product Type | Wall Plate 2G Blank Light Almond |
| Special Features | Standard size plastic smooth wall plate |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007190625 |
| Manufacturers Part Number | SP23-LA |
| UPC | 785007190625 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | Wall Plate |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 200 |
| Weight Per each | 0.1459 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | UL, CSA, CSA, UL514 |