



## DECORATOR OPENINGS, TWO GANG, IVORY

SP262I | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Plate Plastic 2gang 2sierraplex Without Line Ivory



- Molded of non-combustible mar-proof material.
- Available in "SP" series in Standard, Junior-Jumbo, and Jumbo sizes.
- Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.
- Individually wrapped with color-matching screws.
- Resistant to discoloration, grease, oil, solvent, and moisture.
- Nominal thickness, .070 inch.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory  
Size: Standard  
Style: Decorator

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPSC: 39121704  
UR: No

#### DIMENSIONS

Weight: 0.08603

**TECHNICAL INFORMATION**

Material: Thermoset Plastic

Capacity: 2-gang

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant





## DECORATOR OPENINGS, TWO GANG, IVORY

SP262I | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Plate Plastic 2gang 2sierraplex Without Line Ivory



- Molded of non-combustible mar-proof material.
- Available in "SP" series in Standard, Junior-Jumbo, and Jumbo sizes.
- Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.
- Individually wrapped with color-matching screws.
- Resistant to discoloration, grease, oil, solvent, and moisture.
- Nominal thickness, .070 inch.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Ivory  
Size: Standard  
Style: Decorator

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: Yes  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPSC: 39121704  
UR: No

#### DIMENSIONS

Weight: 0.08603

**TECHNICAL INFORMATION**

Material: Thermoset Plastic

Capacity: 2-gang

**BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

