

Eaton SPD2K0225

Catalog Number: SPD2K0225

Eaton NEMA 1 Surface mount, Accepts PD2, 3-Pole, 225A frame MCCB

General specifications



Photo is representative

Product Name	Catalog Number
Eaton enclosed circuit breaker	SPD2K0225
UPC	Product Length/Depth
786689661854	23.8 in
Product Height	Product Width
9 in	9 in
Product Weight	Certifications
14.3 lb	CSA Certified
	UL Listed

Catalog Notes

Power Defense Enclosure - not approved for Series C/G MCCB

Product specifications

Type

CIRCUIT BREAKER ENCLOSURE

Amperage Rating

225 A

Enclosure

NEMA 1

Mounting Method

Surface mounting

Number of poles

Three-pole

Resources

Specifications and datasheets

[Eaton Specification Sheet - SPD2K0225](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton SPD2K0225

Catalog Number: SPD2K0225

Eaton NEMA 1 Surface mount, Accepts PD2, 3-Pole, 225A frame MCCB

General specifications



Photo is representative

Product Name	Catalog Number
Eaton enclosed circuit breaker	SPD2K0225
UPC	Product Length/Depth
786689661854	23.8 in
Product Height	Product Width
9 in	9 in
Product Weight	Certifications
14.3 lb	CSA Certified UL Listed

Catalog Notes

Power Defense Enclosure - not approved for Series C/G MCCB

Product specifications

Type

CIRCUIT BREAKER ENCLOSURE

Amperage Rating

225 A

Enclosure

NEMA 1

Mounting Method

Surface mounting

Number of poles

Three-pole

Resources

Specifications and datasheets

[Eaton Specification Sheet - SPD2K0225](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)