

# Specifications



Photo is representative



## Eaton SPD2K0225

Eaton NEMA 1 Surface mount, Accepts PD2, 3-Pole, 225A frame MCCB

### General specifications

<b>PRODUCT NAME</b>	Eaton enclosed circuit breaker
<b>CATALOG NUMBER</b>	SPD2K0225
<b>UPC</b>	786689661854
<b>PRODUCT LENGTH/DEPTH</b>	23.8 in
<b>PRODUCT HEIGHT</b>	9 in
<b>PRODUCT WIDTH</b>	9 in
<b>PRODUCT WEIGHT</b>	14.3 lb
<b>CERTIFICATIONS</b>	CSA Certified UL Listed
<b>CATALOG NOTES</b>	Power Defense Enclosure - not approved for Series C/G MCCB



Powering Business Worldwide

## Product specifications

<b>TYPE</b>	CIRCUIT BREAKER ENCLOSURE
<b>AMPERAGE RATING</b>	225 A
<b>ENCLOSURE</b>	NEMA 1
<b>MOUNTING METHOD</b>	Surface mounting
<b>NUMBER OF POLES</b>	Three-pole

## Resources

### SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet -  
SPD2K0225](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.

