

# Combination Wall Plate, 1 Blank & 1 Decorator, Two Gang, 302 Stainless Steel

SS1426



Combination Wall Plate, 1 Blank & 1  
Decorator, Two Gang, 302 Stainless Steel



## features & benefits

- Type 302 Stainless Steel, non-magnetic: .032" nominal thickness.
- Brushed finish.
- This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.
- Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

## specifications

### General Info

Size: Standard  
Type: Combination  
Style: Decorator

### Listing Agencies/Third Party Information

CSA Listing Info: Yes  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPS C: 39121704  
UR: No

**Technical Information**

Material: 302 Stainless Steel  
Capacity: 2-gang

**Buy American Act Compliance**

Country of Origin: UNITED-STATES-OF-AMERICA  
Buy American Act Status: Buy American Act Compliant