



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SS403 3WAY In-Wall Dig TMR

*Nsi Industries*

Catalog Number	SS403
Manufacturer	Nsi Industries
Description	Interval Timer 24 HR 120-277V White
Weight per unit	0.3900 (lbs/each)
Product Category	Electronic Time Switches

### Features

action	SPST
Base	Screw
Contact Rating	120-230-277 VAC
Phase	Single Phase
Poles	1
Timing Range	7 DAY

### Dimensions and Weight

Size	H=5.00 - W=3.00
------	-----------------

### Descriptions

Description	3WAY IN-WALL DIG TMR
extra long description	TORK SS403 Interval Timer 24 Hr 120
Features	Tork Digital Interval Timer w/o Neutral APPLICATIONS: Offices, Meeting Rooms, Energy Code Timed Override, Exhaust Fans, Equipment Rooms, Closets, Storage Spaces. FEATURES: COLOR: White (single gang decorator wall plate included) ENERGY CODE PRESET: 2 hour timing for Title 24 and IECC (default) 4 hour timing for ASHRAE 90.1 (with quick dip switch adjustment) PROGRAMMABLE: 5 minutes to 25 hour: 5 minute steps from 5 minutes to 1 hour 10 minute steps from 1 to 4 hours 30 minute steps from 4 to 12 hours 1 hour
Long Description	Interval Timer 24 Hr 120-277V White
Product Type	Interval Timer 24 HR 120-277V White
Special Features	White 7 Day In Wall Time Switch

### Manufacturer Information

Brand	NSi
GTIN	00786261140296
Manufacturers Part Number	SS403
UPC	786261140296

### Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	Digital Auto Off In Wall Time Switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.39

## Uses, Certifications, and Standards

Application	NSI
environmental conditions	32 - + 104 F
Frequency Rating	50-60 Hz
Mounting	Screw Mount
Operating Temperature	32 - + 104 F
standard	cULus