



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SSM38BR 3/8"-16 Metal Drilling Bottom Mount Rod Hanger

L.H. Dottie CO.

Catalog Number	SSM38BR
Manufacturer	L.H. Dottie CO.
Description	Bottom Mount Rod Hanger, Steel Material, 1/4-20 X 1-1/2 In. Size, 1 Nut, 0.036 to 0.188 In. Self Drilling Range, #3 Point Style
Weight per unit	0.0820 (lbs/each)
Product Category	Anchors & Fasteners

Features

Material	Steel
Point Style	#3

Dimensions and Weight

Diameter	1/4
Length	1-1/2
Size	1/4-20 x 1-1/2

Descriptions

Description	3/8"-16 METAL DRILLING BOTTOM MOUNT ROD HANGER
extra long description	DOTTIE SSM38BR 3/8-16 Metal Drillin
Long Description	Bottom Mount Rod Hanger, Steel material, 1/4-20 x 1-1/2 in. Size, 1 nut, 0.036 to 0.188 in. self drilling range, #3 point style
Product Type	3/8-16 Metal Drilling Rod Hanger (Bottom Mount)
Special Features	Features: Self-Drilling

Manufacturer Information

Brand	LH DOTTIE
GTIN	00781002175926
Manufacturers Part Number	SSM38BR
UPC	781002175926

Taxonomies, Classifications, and Categories

Category Description	FASTENERS
Type	Bottom Mount Rod Hanger

Packaging

Carton	100
Weight Per each	0.082

Uses, Certifications, and Standards

Application	Concrete, Pipe Hanging, Conduit, Eye Rod, Cable Trays, Lighting Systems, Strut Channels, Overhead Utilities, Sprinkler Systems, Drop Ceilings, HVAC Duct, Electrical, Refrigeration
-------------	---